

SPECIFICATIONS

Material: Standard Seeloc® washer is 300 series stainless steel, but can be made in nickel-plated carbon steel, aluminum, etc. Silicone rubber is standard.

Temperature Range: -160° F to +500° F (-106° C to +260° C)


Pressure Range: Exceeds 100 psi internal and external

Shelf Life: Excess of 25 years.

Resistant to: Salt spray, sunlight, ozone, weather, acids and etc.

Installation: Seeloc® washers are installed on bolts, studs or screws in the same manner as regular washers. The rubber section should always face the panel, mounting surface.

Rating: IP66/68 UL Recognized for type 4X & Type 6 Enclosure Protection.



ITEM NUMBER	THREAD SIZE	WASHER O.D.
75601	#6	0.550"± 0.050
75801	#8	0.550"± 0.050
75101	#10	0.550"± 0.050
75602	#6	1"± 0.050
75802	#8	1"± 0.050
75102	#10	1"± 0.050
75082	#1/4	1"± 0.050
75107	#5/16	1"± 0.050
75122	#3/8	1"± 0.050
75142	#7/16	1"± 0.050
75162	#1/2	1"± 0.050
75603	#6	1-1/2"± 0.050
75803	#8	1-1/2"± 0.050
75103	#10	1-1/2"± 0.050
75083	#1/4	1-1/2"± 0.050
75108	#5/16	1-1/2"± 0.050
75123	#3/8	1-1/2"± 0.050
75143	#7/16	1-1/2"± 0.050
75163	#1/2	1-1/2"± 0.050
75173	#5/8	1-1/2"± 0.050
75183	#7/8	1-1/2"± 0.050

D	ECO-14-0006: ADDED PERMISSIBLE NOTE, ADDED THREAD SIZE/DIMENSION NOTE AND RATING INFOR. DWN: D. LAW CHKD BY: KF/FK.				11.17.14	
C	ADDED 75183				05.19.10	
B	CHANGED DWG. NO. FROM SW-100 TO 7500 SERIES, CHANGED WAS O.D. FOR S. GOK 75601, 75801 AND 75101, ADDED TOLERANCE				07.14.08	
A	CAD COMPUTER GENERATED				12.23.02	
REV.	DESCRIPTION				DATE	
MAXIMUM AND MINIMUM MEASURE- MENTS ARE STATED DIRECTLY ON EACH DIMENSION.		TITLE: SEELOC® VIBRATIO-RESISTANT, SELF-SEALING WASHERS		ENG.	S. GOK	07.14.08
				DWN:	S. GOK	07.14.08
MAT'L: AS NOTED		APM-HEXSEAL CORPORATION		CHKD.	J CELLA	07.14.08
FINISH: AS NOTED				SCALE	DWG.NO. 75000 SERIES	

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.

THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.