

1		2		3		4		5			
										TECHNICAL CHARACTERISTICS MATERIAL INSULATOR: PBT FLAMABILITY RATING: UL94-V0 COLOR: BLACK CONTACT MATERIAL: COPPER ALLOYS CONTACT TYPE: STAMPED CONTACT PLATING: SELECTIVE GOLD SHIELDING: BRASS WITH Ni PLATING QUALITY CLASS: 1500 MATING CYCLES ENVIRONMENTAL OPERATING TEMPERATURE: -40 UP TO 105°C COMPLIANCE: LEAD FREE AND ROHS ELECTRICAL CURRENT RATING: 1.0 A max WORKING VOLTAGE: 30 VAC INSULATOR RESISTANCE: >1000 MOHM DIELECTRIC WITHSTANDING VOLTAGE: 750 VAC/MN CONTACT RESISTANCE: 20 mOHM MAX STANDARD CERTIFIED: E323964 SOLDERING JEDEC LEAD FREE WAVE SOLDERING PROCESS PACKAGING TUBE	
RECOMMENDED PCB LAYOUT RECOMMENDED PCB THICKNESS : 1.6 mm											
RoHS Compliant				PROJECTION:		GENERAL TOLERANCE					
						.X = +/_ 0.2 .XX = +/_ 0.15					
				APPROVAL: NPr		UNIT: MM		DESCRIPTION: MINI USB 2.0 TYPE B 5 CONTACTS			
L 26-NOV-15 PACKAGING AK						SCALE:					
K 09-AVR-15 PCB THICKNESS QP						SHEET: 1/2		WERI PART NO: 651 005 136 521			
J 18-FEB-13 DESIGNATION AR						DRAW: DXS					
I 08-NOV-11 CURRENT RATING GG											
H 22-JUN-11 CURRENT RATING GG											
REV DATE FILE BY											

A4

