






REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED PER ECR-13-012557	07AUG2013	MVE	OL
	A1	ECR-16-001206	27JAN2016	KR	MvE
	A2	ECR-16-005694	19APR2016	KR	MvE



NOTES.

- MATERIALS:
HOUSING: GLASS FILLED PBT
COLOR: NATURAL/WHITE
CONTACTS: SILVER PLATED COPPER ALLOY
 - FOR SOLID AND STANDARD WIRE AWG 22-18
 - COMPLIES WITH DIRECTIVE 2002/95/EC (ROHS)
 - M3 SCREW TO BE USED FOR MOUNTING
- △ 5 DATE CODE YY-WW-D ANY WHERE EXCEPT OVER LOGO OR +/- SIGN.

2213258-1 AS SHOWN

Z50 LED HOLDER LOW PROFILE

PART NO	DESCRIPTION
2213258-2	Z50 LED HOLDER STANDARD PROFILE 2121
2213258-1	Z50 LED HOLDER LOW PROFILE 2121

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±-
	1 PLC ±-
	2 PLC ±-
	3 PLC ±-
	4 PLC ±-
	ANGLES ±-
MATERIAL	FINISH
-	-
-	-

DWN	07AUG2013
M.V.ESSEN	
CHK	07AUG2013
M.V.ESSEN	
APVD	07AUG2013
O.I.FIJNSE	
PRODUCT SPEC	108-133008
APPLICATION SPEC	114-32048
WEIGHT	-
CUSTOMER DRAWING	

 TE Connectivity		NAME	
		LUMAWISE Z50 LED HOLDER ASSY 2121	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2213258	-
SCALE		SHEET	REV
2:1		1 OF 3	A2

THIS DRAWING IS UNPUBLISHED.





RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



2213258-2 AS SHOWN

Z50 LED HOLDER STANDARD PROFILE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.V.ESSSEN 07AUG2013	 TE Connectivity NAME LUMAWISE Z50 LED HOLDER ASSY 2121					
DIMENSIONS: mm		CHK M.V.ESSSEN 07AUG2013				SIZE	CAGE CODE	DRAWING NO
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD O.IEIJNSE 07AUG2013				A3	00779	C-2213258
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC 108-133008				RESTRICTED TO		
MATERIAL		FINISH	WEIGHT		SCALE			
-		-	-		2:1			
-		-	CUSTOMER DRAWING		SHEET 2 OF 3			
					REV A2			

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

REVISIONS

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

THE SKETCH BELOW IS SHOWING THE NOMINAL LED COB DIMENSION TO MATCH WITH THE Z50 LED HOLDER 2121

FOR TECHNICAL DETAILS ABOUT A PROPER MATCH WITH A SPECIFIC LED COB ARRAY PLEASE CONTACT A REPRESENTATIVE AT TE-CONNECTIVITY

Technical drawing of a square LED COB array. The square has a side length of 21.5 mm. A circular LED COB array is centered within the square, with the letters "LES" inside. The center of the COB array is 7.5 mm from the top edge and 7.7 mm from the right edge. A contact point is located at the intersection of the 7.5 mm and 7.7 mm dimensions. A dimension of 21.5 mm is also shown from the center of the COB array to the bottom edge. Below the square, a cross-section of a holder is shown with a thickness of 1.0 mm and a width of 0.9 mm.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN M.V.ESSSEN 07AUG2013

CHK M.V.ESSSEN 07AUG2013

APVD O.I.FIJNSE 07AUG2013

PRODUCT SPEC

108-133008

APPLICATION SPEC

114-32048

WEIGHT -

CUSTOMER DRAWING

STE

TE Connectivity

NAME

LUMAWISE
Z50 LED HOLDER ASSY 2121

RESTRICTED TO

SIZE CAGE CODE DRAWING NO

A3 00779 C-2213258

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL

-

FINISH

-

1470-19 (3/13)

SCALE 4:1

SHEET 3 OF 3

REV A2