

MICRO SWITCH

FREEPORT ILLINOIS U S A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BA-1RV5435246-A2

BA-1RV5435246-A2

PAGE 1 OF 1

DRAWING
NUMBER

5

ISSUE

REPLACES X 71636-B A

RELEASE NO. PR-11436T

CHECK

REVISIONS

A	CO-73287-J	JAL	22 NOV 93
B	CO-7758R	MAM	29 MAR 94
C	CO93346	DLT	31 AUG 98
D	CO93921	GJW	13 JAN 99

CHECK

10 A/C 82


CER

82 CHECK

D J S 6 AUG 82

FORMTEK

FD-52848-A




NOTES

- △ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000±.002 CENTERS
- 2 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE ----- 1.5 OZ MAX
RELEASE FORCE ----- 1/2 OZ MIN
DIFFERENTIAL TRAVEL ----- .030 MAX
OVERTRAVEL ----- .060 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

CODE L65 15A-125, 250 OR 480 VAC
1/2HP-125 VAC, 1HP-250 VAC
L288
L299
L306
16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS - CONVERSIONS ARE ONLY FOR REFERENCE - UNLESS NOTED - TOLERANCES ARE 2

NO PLACES	DIM	TOL	DIM	TOL
ONE PLACE	X	1/64	X	0.015
TWO PLACES	X, X	0.0015	X, X	0.0015
THREE PLACES	X, X, X	0.0005	X, X, X	0.0005
ANGLES				

DESIGN UNITS ☐ SI METRIC ☒ US CUSTOMARY

WEIGHT .063 LB