

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
© COPYRIGHT - By - TE CONNECTIVITY		ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H2	ECR-16-011710	22AUG2016	N.L	D.Z

YES	71.12[2.800]	28	5-643815-8
YES	68.58[2.700]	27	5-643815-7
YES	66.04[2.600]	26	5-643815-6
YES	63.50[2.500]	25	5-643815-5
YES	60.96[2.400]	24	5-643815-4
YES	58.42[2.300]	23	5-643815-3
YES	55.88[2.200]	22	5-643815-2
YES	53.34[2.100]	21	5-643815-1
YES	50.80[2.000]	20	5-643815-0
YES	48.26[1.900]	19	4-643815-9
YES	45.72[1.800]	18	4-643815-8
YES	43.18[1.700]	17	4-643815-7
YES	40.64[1.600]	16	4-643815-6
YES	38.10[1.500]	15	4-643815-5
YES	35.56[1.400]	14	4-643815-4
YES	33.02[1.300]	13	4-643815-3
YES	30.48[1.200]	12	4-643815-2
YES	27.94[1.100]	11	4-643815-1
YES	25.40[1.000]	10	4-643815-0
YES	22.86[.900]	9	3-643815-9
YES	20.32[.800]	8	3-643815-8
YES	17.78[.700]	7	3-643815-7
YES	15.24[.600]	6	3-643815-6
YES	12.70[.500]	5	3-643815-5
YES	10.16[.400]	4	3-643815-4
YES	7.62[.300]	3	3-643815-3
YES	5.08[.200]	2	3-643815-2

NO	71.12[2.800]	28	2-643815-8	SUPERSEDED BY 5-643815-8	
NO	68.58[2.700]	27	2-643815-7	SUPERSEDED BY 5-643815-7	
NO	66.04[2.600]	26	2-643815-6	SUPERSEDED BY 5-643815-6	
NO	63.50[2.500]	25	2-643815-5	SUPERSEDED BY 5-643815-5	
NO	60.96[2.400]	24	2-643815-4	OBSOLETE	
NO	58.42[2.300]	23	2-643815-3	SUPERSEDED BY 5-643815-3	
NO	55.88[2.200]	22	2-643815-2	SUPERSEDED BY 5-643815-2	
NO	53.34[2.100]	21	2-643815-1	SUPERSEDED BY 5-643815-1	
NO	50.80[2.000]	20	2-643815-0		
NO	48.26[1.900]	19	1-643815-9	SUPERSEDED BY 4-643815-9	
NO	45.72[1.800]	18	1-643815-8	SUPERSEDED BY 4-643815-8	
NO	43.18[1.700]	17	1-643815-7	OBSOLETE	
NO	40.64[1.600]	16	1-643815-6		
NO	38.10[1.500]	15	1-643815-5	SUPERSEDED BY 4-643815-5	
NO	35.56[1.400]	14	1-643815-4		
NO	33.02[1.300]	13	1-643815-3	SUPERSEDED BY 4-643815-3	
NO	30.48[1.200]	12	1-643815-2	SUPERSEDED BY 4-643815-2	

NO	27.94[.1.100]	11	1-643815-1
NO	25.40[1.000]	10	1-643815-0
NO	22.86[.900]	9	643815-9
NO	20.32[.800]	8	643815-8
NO	17.78[.700]	7	643815-7
NO	15.24[.600]	6	643815-6
NO	12.70[.500]	5	643815-5
NO	10.16[.400]	4	643815-4
NO	7.62[.300]	3	643815-3
NO	5.08[.200]	2	643815-2
LEADFREE	DIM A	NO. OF CIRCUITS	PART NO.

1 MATERIAL: CONNECTOR - NYLON UL94V-2 (BLUE).
CONTACTS - 0.30[.012] THICK COPPER ALLOY
BRIGHT TIN-LEAD .00203[.000080] MIN THICKNESS
FOR 643815-2 THRU 2-643815-8.
MATTE WHISKER MITIGATED TIN .00203[.000080] MIN THICKNESS
OVER NICKEL UNDERPLATE FOR 3-643815-2 THRU 5-643815-8.

2 CONTACTS ACCEPT 26 AWG WIRE WITH 1.52[.060] MAX INSULATION DIAMETER.




3 CONTACTS MUST ACCEPT 0.64 ± 0.03 [$.025 \pm .001$]
POST AND REMAIN LOCKED IN POSITION.

4 IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.

5 DIMENSIONS IN BRACKETS ARE IN INCHES.

6 HOUSING FEATURES ARE: CLOSED END WITH
LOCKING RAMP AND WITH POLARIZING TAB.

7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI




54.3815

1

A

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 11JUN2003 CHK D. BOSSI 11JUN2003 APVD D. BOSSI 11JUN2003		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 0.13 [.005] 4 PLC ± ANGLES ±		NAME MTA 100 CONNECTOR ASSEMBLY, 26 AWG, STANDARD	
		PRODUCT SPEC 108-1050 APPLICATION SPEC 114-1019		SIZE A2	
MATERIAL 		FINISH 		CAGE CODE 00779	
		WEIGHT 0		DRAWING NO C-643815	
CUSTOMER DRAWING				SCALE 5:1	
				SHEET 1 OF 1	
				REV H2	