

UNCONTROLLED DOCUMENT





ELECTRO-OPTICAL CHARACTERISTICS TA =25°C If=20mA							
PARAMETER	MIN	TYP.	MAX	UNITS	TEST COND		
PEAK WAVELENGTH		565		nm			
FORWARD VOLTAGE		2.2	2.8	Vf			
REVERSE VOLTAGE	5.0			Vr	Ir=100μA		
AXIAL INTENSITY		10		mcd	If=20mA		
VIEWING ANGLE		140		2x theta			

SML-LX0805GC-TR

E.C.N. #10BRDR. & REDRAWN.

E.C.N. #10BRDR. & REDRAWN.

E.C.N. #10862.

E.C.N. #10967.

E.C.N. #11148.

E.C.N. #11508.

E.C.N. #10644 & REDRAWN IN 3D.

E.C.N. NUMBER AND REVISION COMMENTS

REV.

G

REV.

В

С

D

Ε

F

G

PART NUMBER

DATE

08.26.98

07.18.00

05.09.02

03.14.03

03.06.09

01.17.05

06.20.11

	EMITTED COLOR: EPOXY LENS FINISH:	GREEN WATER CLEAR			
C	LIMITS OF SAFE OPERATION	AT 25°C			
	PARAMETER		MAX	UNITS	
	PEAK FORWARD CURRENT*		160	mA	


PEAK FURWARD CURRENTS	160	mA.
STEADY CURRENT	30	mA
POWER DISSIPATION	100	mW
DERATE FROM 25°C	-1.2	mW/*C
OPERATING TEMP.	-40 TO +85	•C
STORAGE TEMP.	-40 TO +85	•C

F D	CAUTION: MOISTURE SENSITIVE DEVICE	
	PER JEDEC LEVEL 2 STANDARDS	




ANODE ○──□── CATHODE

0.60 [0.024]	
•	







*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= $^{+0.00}_{-0.00}$ MAX.= $^{+0.00}_{-0.000}$ MAX.= $^{+0.000}_{-0.000}$ MAX.= $^{+0.00}_{-0.000}$ MAX.= $^{+0.000}_{-0.000}$ MAX.= $^{+0.000}_{-0.000}$ UNCONTROLLED DOCUMENT



290 E. HELEN ROAD PALATINE, IL 60067-6976 PHONE: +1.847.359.2790 FAX: +1.847.359.6538 WEB: WWW.LUMEX.COM MEMBER OF ITW PHOTONICS GROUP 2.0mm X 1.25mm PCB SURFACE MOUNT, 565nm GREEN LED, WATER CLEAN LENS, TAPE & REEL, 3K PER REEL.

THE SPECIFICATIONS MAY CHANGE AT ANY TIME WITHOUT NOTICE DUE TO NEW MATERIALS OR PRODUCT IMPROVEMENT.


CONFIDENTIAL INFORMATION
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

DATE:	06	5.20.	11	DRAWN BY:	AB
PAGE:	1	OF	2	CHKD BY:	KF
SCALE:		NTS		APRVD BY:	KF
UNIT: mm [INCH]		(Pb)			


UNCONTROLLED DOCUMENT

PART NUMBER	SML-LX0805GC-TR	REV.	G
DATE	E.C.N. NUMBER AND REVISION COMMENTS		REV
08.26.98	E.C.N. #10BRDR. & REDRAWN.		Α
07.18.00	E.C.N. #10644 & REDRAWN IN 3D.		В
05.09.02	E.C.N. #10862.		С
03.14.03	E.C.N. #10967.		D

LEAD FREE REFLOW PROFILE



TOTAL TIME ABOVE 220°C IS 60 SECONDS MAX.



1. POLARITY MARK IS ORIENTED TOWARDS TAPE SPROCKET HOLE.

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= $^{+DECIMAL}_{-0.00}$ PRECISION MAX.= $^{+0.00}_{-0.00}$ MAX.= $^{+0.00}_{-0.00}$ PRECISION ARE: X=±1 (±0.039), X.XX=±0.5 (±0.020), X.XX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD SIZE=±0.05 (±0.002), LEAD SIZE=±0.05 (±0.003). MIN= $^{+DECIMAL}_{-0.00}$ PRECISION MAX.= $^{+0.00}_{-0.00}$ MAX.= $^{+0.00}_{-0.00}$

Creating LED and LCD Solutions Together

290 E. HELEN ROAD PALATINE, IL 60067-6976 PHONE: +1.847.359.2790 FAX: +1.847.359.6538 WEB: WWW.LUMEX.COM MEMBER OF ITW PHOTONICS GROUP 2.0mm X 1.25mm PCB SURFACE MOUNT, 565nm GREEN LED, WATER CLEAN LENS, TAPE & REEL, 3K PER REEL

THE SPECIFICATIONS MAY CHANGE AT ANY TIME WITHOUT NOTICE DUE TO NEW MATERIALS OR PRODUCT IMPROVEMENT.

CONFIDENTIAL INFORMATION
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

UNCONTROLLED DOCUMENT DATE: 06.20.11 DRAWN BY: AΒ

PAGE: 2 OF 2 CHKD BY: KF SCALE: NTS APRVD BY: KF UNIT: mm [INCH]

(Pb)