



DESIGNED & DIMENSIONED
IN MILLIMETERS [INCHES]

HDBNC-P-C-XX-ST-CA8X

GENDER
-P: PLUG

TYPE
-C: CABLE

CRIMP OPTION
(LEAVE BLANK FOR SOLDERED CENTER CONTACT)
-C: CRIMPABLE CENTER CONTACT




TERMINATION
-CA8


ORIENTATION
-ST: STRAIGHT

PLATING SPECIFICATION

- HF: 30µ" GOLD CENTER CONTACT,
3µ" GOLD OUTER CONTACT
100µ" NICKEL ON OTHER COMPONENTS
- HN: 30µ" GOLD CENTER CONTACT,
100µ" NICKEL OUTER CONTACT
- GF: 10µ" GOLD CENTER CONTACT,
3µ" GOLD OUTER CONTACT
100µ" NICKEL ON OTHER COMPONENTS
- GN: 10µ" GOLD CENTER CONTACT,
100µ" NICKEL OUTER CONTACT

DO NOT
SCALE FROM
THIS PRINT



| | | |
|---|--|---|
| <p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. TOLERANCES ARE: DECIMALS ANGLES X.X: ±0.3 [.01] 5° X.XX: ±0.13 [.005] X.XXX: ±0.051 [.0020]</p> | <p>PROPRIETARY NOTE THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.</p> |  <p>520 PARK EAST BLVD., NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code 55322</p> |
| <p>MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 3:1 COUPLING NUT, SHELL, BODY, PIN, FERRULE : BRASS GASKET: SILICONE C-RING, FLAT WASHER: BRASS SPRING: STAINLESS STEEL DIELECTRIC: PTFE</p> | | <p>DESCRIPTION: HD BNC 75 OHM, ST PLUG FOR CCA-1855A CABLE DWG. NO. HDBNC-P-C-XX-ST-CA8X BY: ALVIN W 02/16/2011 SHEET 1 OF 1</p> |