


Notes:

1. Only RoHS Compliant Processes and Materials used for this assembly.
2. Marking to Contain "ConductRF", Part No. & Serial No., Black Text.
3. Mark BLUE Shrink Tube on both connectors ends with "DC-27GHz" & Connector Series
4. Single Centered Marker up to 15'(4.5M), Two Markers 12"(30cm) from ends for lengths over 15'(4.5M)
5. Sweep Tested for DC to 27GHz, Plot Data and Store.
6. Serial No. to be Marked as Cxxxxx, where xxxxx = sequential no. from log.
7. Caps to be Fitted Prior to Packaging
8. Cables to be Coiled and Placed in Anti-Static Bag with ConductRF Label. (See Separate Label Instructions)

TESTeCON Los Loss RF Test Cable



ConductRF
TSX74-S1S1-XXX
S/N-Cxxxxx

Marker Example

L	XXX	Max Insertion Loss(dB) 27GHz
2ft	F02	1.213
4ft	F04	2.056
5ft	F05	2.477
6ft	F06	2.898
10ft	F10	4.583
12ft	F12	5.426
20ft	F20	8.796
1M	1M0	1.753
VSWR(max)		1.40:1

Part No. Configurator - XXX

FXX = Length in Feet (eg F03=3ft)
 SXX = Length in Inches (eg S18=18")
 XMX = Length in Meters (eg 2M5=2.5m)
 CXX = Length in CM (eg C50=50cm)

					Customer DWG	Title: SMA Male to Male, 27GHz Flexible Test Cable, Low Loss				
					Remarks:	Originated: 01/26/16	Conduct RF sales@ConductRF.com Tel: +1 978 374 6840	Range: TSA74		Sheet 1 of 1
1	Pre-Release		DG	06/23/16		Dwg Ref: TSX74-S1S1				
REV.	DESCRIPTION	ECN	DRAWN	DATE	Tolerances: Length +/-2%	Checked: JW	Approved: PL	Rev: 1	Part No: TSX74-S1S1-XXX	
REVISION HISTORY										