



- NOTES
1. 嵌合相手 : 502439-**00
MATE WITH : 502439-**00
 2. 端子テール部 及び ネイルの平坦度: 0.1MAX.
TAIL AND NAIL COPLANARITY TO BE 0.1 MAX.
 - △3 偶数極に適用。
APPLY FOR CKT. SIZE = EVEN.
 4. 端子テール部 及び ネイルに錫めっきを使用しているため、
外観に摺動痕が付く場合が御座います。
THE WOUND OF FRICTION MIGHT ADHERE TO EXTERNALS
BECAUSE THE TIN PLATING IS USED FOR THE TAIL AND NAIL.
 5. 本製品のプラスチック部に黒点等が確認される場合や
色合いが異なる場合がありますが、製品性能に影響はありません。
THERE IS NO INFLUENCE IN THE PRODUCT PERFORMANCE THOUGH
THE BLACK SPOT ETC. MIGHT BE CONFIRMED TO THE PLASTIC PART
OF THIS PRODUCT AND THE SHADE MIGHT BE DIFFERENT.
 6. ELV 及び RoHS 適合品
ELV AND RoHS COMPLIANT






嵌合図 MATED CONNECTOR
(SCALE : 2-1)


9.2	32	28	34	502494-1570	15
5.2	30	26	32	502494-1470	14
5.2	28	24	30	502494-1370	13
5.2	26	22	28	502494-1270	12
5.2	22	18	24	502494-1070	10
5.2	18	14	20	502494-0870	8
4	14	10	16	502494-0670	6
7.6	10	6	12	502494-0470	4
4.8	8	4	10	502494-0370	3
2.8	6	2	8	502494-0270	2
D	C	B	A	EMBOSSED TAPE PACKAGE 注文番号 ORDER NO.	極数 CKT.NO.



番号 NO.	部品 PART	材質 MATERIAL			
①	ハウジング HOUSING	耐熱性樹脂 UL94V-0 色 : ナチュラル HEATPROOF RESIN UL94V-0 COLOR:NATURAL			
②	ターミナル TERMINAL	銅合金 COPPER ALLOY			
		錫めつき : 1.0 micro-meter MIN. TIN (TAIL AREA)			
		ニッケルめつき(下地) : 1.0micro-meter MIN. NICKEL (UNDER PLATING)			
③	ネイル NAIL	銅合金 COPPER ALLOY			
		錫めつき : 1.0 micro-meter MIN. TIN			
		ニッケルめつき(下地) : 1.0micro-meter MIN. NICKEL (UNDER PLATING)			
RELEASE STATUS		P1	RELEASE DATE	12.07.2016	06:58:54

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
REVISED	EC NO: 106544 DRWN: QHE31 CHK'D: SAKIYAMA APPR: TKANEKO	2016/07/12 2016/07/12 2016/07/12	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex®					
						MM		4:1							
			ANGULAR TOL ± 3.0 °			DRWN BY		DATE		CLIK-MATE 2.0MM PITCH W/B CONN. RA TYPE REC. ASSY 2-15CKT					
						AISHIKAWA		2016/04/19							
			4 PLACES ± 0.2			CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING					
						KOMURAKAMI		2016/04/28							
			3 PLACES ± 0.2			APPR BY		DATE		SERIES 502494 MATERIAL NUMBER SEE TABLE CUSTOMER GENERAL					
						TKANEKO		2016/04/28							
2 PLACES ± 0.2			DRAWING SIZE		THIRD ANGLE PROJECTION		DOCUMENT NUMBER 5024941509 DOC TYPE PSD DOC PART 000 SHEET NUMBER 1 OF 2								
			A3												
1 PLACE ± 0.2			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												
0 PLACES ± 0.2															
B	REV														



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
REVISED	EC NO: 106544 DRWN: QHE31 CHK'D: SAKIYAMA APPR: TKANEKO	2016/07/12 2016/07/12 2016/07/12	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 3.0 ° 4 PLACES ± 0.2 3 PLACES ± 0.2 2 PLACES ± 0.2 1 PLACE ± 0.2 0 PLACES ± 0.2 DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION UNITS		SCALE		molex® CLIK-MATE 2.0MM PITCH W/B CONN. RA TYPE REC. ASSY 2-15CKT							
					MM		4:1									
					DRWN BY		DATE									
					AISHIKAWA		2016/04/19		CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING			
					KOMURAKAMI		2016/04/28		APPR BY		DATE					
					TKANEKO		2016/04/28		DRAWING SIZE		THIRD ANGLE PROJECTION					
					A3				SERIES		MATERIAL NUMBER		CUSTOMER			
					502494		SEE TABLE		GENERAL		DOCUMENT NUMBER		DOC TYPE		DOC PART	
					5024941509		PSD		000		SHEET NUMBER		2 OF 2			

