

MATERIALS AND FINISHES


SMA PLUG: (73251-4980)
SEE SD-73251-498

SMP JACK: (73406-6680)
SEE SD-73406-668

CABLE:
TEMP-FLEX 100054-0006

LABEL:
BRADY PERMASLEEVE

SHRINK TUBE:
VERSAFIT OR EQUIVALENT



89762-1403	120.0±2.25	3048±57.15	10.0
89762-1402	12.00±.50	304.8±12.70	1.45
89762-1401	9.00±.25	228.6±6.35	1.07
89762-1400	6.00±.25	152.4±6.35	0.70
PART NO.	IN	MM	MAX INSERTION LOSS TO 26 GHz (dB)
	A		

MAX VSWR 1.50 @ 26 GHz

CHG: CABLE WAS TEMP-FLEX 086-2201 IN MAIN VIEW, TITLE BLOCK & MAT'L & FINISHES. ADD TOLERANCES TO "A" DIMENSIONS. EC NO: URF2016-0590 2016/02/26 DRAWN:MEIER 2016/02/29 CHKD:SSS APPR:AROBERTSON 2016/03/02 A3	REV	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
						DRAWN BY	DATE	TITLE CA SMA P STR / SMP J STR 100054-0006 CABLE EWR-5133, CA-SMA/SMP molex			
						CHECKED BY	DATE				
						APPROVED BY	DATE				
						MATERIAL NO.	DOCUMENT NO.				SHEET NO.
						SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
				4 PLACES ± --- ± ---		JLEE02 2013/03/27					
				3 PLACES ± --- ± ---		2013/03/27					
				2 PLACES ± --- ± ---		2013/03/27					
				1 PLACE ± --- ± ---		2013/11/22					
0 PLACE ± --- ± ---											
ANGULAR ± 2 °		SEE TABLE		SD-89762-140		1 OF 1					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											