



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



ISOMETRIC VIEW  
(SHOWN W/O DUST CAP)




PANDUIT P/N	FIBER SIZE (MICRONS)	WEIGHT
FSTMM**	62.5	.064 LB/10 PCS (29.0 g/10 PCS)
FSTMM50**	50	.064 LB/10 PCS (29.0 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. MATERIAL;
  - BOOTS: PLASTIC
  - CRIMP SLEEVE: BRASS
  - FERRULE: CERAMIC
  - BAYONET: POLYETHERIMIDE
  - SPRING: ZINC PLATED MUSIC WIRE



.38 DIA  
[9.7]



FRONT AND SIDE VIEWS  
(SHOWN W/O DUST CAP)

DRAWING FILENAME	SIZE
M00960AA_DC_01B.PRT (1)	A

ST MULTIMODE PRE-POLISHED CRIMP  
OPTICAL FIBER CONNECTOR (FSTMM)  
CUSTOMER DRAWING

 <b>PANDUIT</b> ™ CORP. TINLEY PARK, ILL 60477	I.I. NUMBER
	PRODUCT SPEC
 THIRD ANGLE PROJECTION	WORK INSTRUCTION
	SCALE NONE
DATE 01-03-01 CHK'D JAW	PART NO. FSTMM** FSTMM50**
	DRAWING NO. 00960-12

ALL DIMENSIONS ARE GIVEN IN INCHES,  
UNLESS OTHERWISE SPECIFIED.  
DIMENSIONAL TOLERANCES ARE:  
(.X) (.XXX) ±.010(.3)  
(.XX) ±.03(.8) ANGLES

MAT'L:

SEE  
NOTES

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
1	04-01-02	MC		B. TITLE BLOCK UPDATED A. FERRULE ASSEMBLY P/N WAS QTM ST	00960-12				
R	01-03-01	MC	JW	RELEASED TO PRODUCTION	00960-12	JW			