



- 1
- CONTACT CAVITIES IDENTIFIED BY CHARACTERS ON FRONT AND REAR OF CONNECTOR.
- 2
- .000030 MIN GOLD FOR A LENGTH OF .200 MIN FROM MATING END, .000100 MIN TIN-LEAD FOR A LENGTH OF DIMENSION "A" FROM OPPOSITE END, ALL OVER .000050 MIN NICKEL.
- 3
- RECOMMENDED PC BOARD HOLE SIZE FOR CONTACT POST = 1.02±0.08[.040±.003] DIA.
- 4
- .000030 MIN GOLD FOR A LENGTH OF .200 MIN FROM MATING END, .000100 MIN TIN FOR A LENGTH OF DIMENSION "A" FROM OPPOSITE END, ALL OVER .000050 MIN NICKEL.



	4	NO	.227	1-206455-2
	4	NO	.449	1-206455-1
PRELIMINARY	4	YES	.671	206455-9
PRELIMINARY	4	YES	.449	206455-8
PRELIMINARY	4	NO	.671	206455-7
OBSOLETE	4	NO	.227	-206455-3-
	4	NO	.227	206455-2
OBSOLETE	4	NO	.449	-206455-1
CONTACT FINISH	4-40 THREADED INSERTS	A	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
J.GALLUCCI
5-30-91

CHK
W.G.LENKER
4-14-92

APVD
K.BEAVER
4-14-92

NAME

PRODUCT SPEC
108-10024

APPLICATION SPEC

SIZE
A1

CAGE CODE
00779

DRAWING NO
206455

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
2:1

SHEET
1 OF 1

REV
U1

TE Connectivity

RECEPTACLE ASSEMBLY, POSTED,
STD SEX, SERIES 1, 23-63, CPC