

SW2014




Revision level			Revision Record	Changed	Date	Approved	Date
Drawing	State	Part					
00.0	Design Release		SEE ECN# 013489	GRW	7/6/2016	KAC	7/6/2016


FEATURES AND BENEFITS:

- BASE AND COVER CLOSE WITH INTERLOCKING MECHANISM.
- MULTIPLE ENTRIES AND TABS TO CONTROL BEND RADIUS AND SECURE CABLES.
- SLIM DESIGN AND CLEAR COVER TO EASILY INSPECT MANAGEMENT FLAWS.
- CAN ACCOMMODATE UP TO 24 SPLICES.
- EQUIPPED WITH 2 OPENINGS FOR MOUNTING TO PROVIDE MORE FLEXIBILITY.
- ROBUST POLYCARBONATE COVER MAKES A VISUAL INSPECTION IMMEDIATE, PERFECTLY SUITED FOR THE FIBER ROUTING, THEIR MAINTENANCE AND TROUBLESHOOTING.

INCLUDED WITH THE PRODUCT (QTY)
 - SELF-ADHESIVE SPLICE HOLDERS (2)




12
[298.2]



7
[178.1]

NOTES:


1. ALL DIMENSIONS ARE IN INCHES AND DIMENSIONS IN BRACKETS ARE IN MILLIMETERS.
2. SPL-MSPL6/12 COVERS ARE MADE OF UL 94V-0 CLEAR PLASTIC.
3. SPL-MSPL6/12 BODYS ARE MADE OF ALUMINIUM SHEET METAL.
4. CERTIFICATION AND COMPLIANCES:
 - UL 94
 - RoHS



4 [102.1]

5/16 [8.1]


SLIM FIBER OPTIC METAL SPLICE TRAY
(12" LENGTH)



4 [102.1]

5/16 [8.1]

SLIM FIBER OPTIC METAL SPLICE TRAY
(7" LENGTH)



FOAM SPLICE HOLDER

Type #	Splices	Length	Article #
FEST12	12	7 in	904-00711
FEST24	24	12 in	904-00712

Material
 ALUMINUM SHEET
 METAL UL94V-0

Units: **inches**
 Dimension without tolerances details to:
 .xxxx = ±.0005
 .xxx = ±.005
 .xx = ±.01
 .x = ±.03
 None = ±.06
 ∠ = ±0.5°
 Dimension Formatted in [mm]

The copyright of this drawing is reserved by HellermannTyton. It is issued on condition that it is not reproduced, copied, or disclosed to a third party, either wholly or in part, without the consent of HellermannTyton.

Drawn GRW 7/5/2016
 Approved KAC 7/5/2016

HellermannTyton
 North America
 Email: corp@htamericas.com
 Web: www.hellermann.tyton.com

Article/Type-No FEST 12 & FEST24

Title **FIBER SPLICE TRAY**

Drawing-No PRODUCTION : Phase

16-1286-001-CSU

Scale 1:1

Project Number
 PRP 16-1286

Format AH

Sheet 1/1