


UNCONTROLLED DOCUMENT











RECOMMENDED SOLDER PAD LAYOUT





SML

ELECTRO-OPTICAL CHARACTERISTICS TA=25°C

E.C.N. #10967

E.C.N. #11157

E.C.N. #11148

E.C.N. #11508

PART NUMBER

DATE 3.14.03

8.10.04

12.03.04

3.05.09

__LX0402UPGC*-*_TR

REV.

 $I_f = 20 \text{mA}$

D

REV.

Α

В

С

D

UNITS

		10 SEC. MAX.
	255	(-)
TEMPERATURE (°C)	160 150	90-120 SEC. \$\frac{1}{2}\text{C/SEC. MAX.}
	25 0	TIME

TOTAL TIME ABOVE 220°C IS 60 SECONDS MAX.

LEAD FREE REFLOW PROFILE

I ANAMETEN
PEAK FORWARD CURR
STEADY CURRENT
POWER DISSIPATION
DERATE FROM 25°C

DADAMETED

LIMITS OF SAFE OPERATION AT 25°C

PEAK FORWARD CURRENT*	160	mA
STEADY CURRENT	25	mA
POWER DISSIPATION	100	mW
DERATE FROM 25°C	- 1.2	mW/°C
BOPERATING TEMP.	- 40 TO +85	*C
STORAGE TEMP.	- 40 TO +85	*C

MAX

* t<10µS

NOTES:

1. PARTS PACKAGED IN CONDUCTIVE COVER AND CARRIER TAPE. 2. THE CATHODE IS ORIENTATED TOWARDS THE TAPE SPROCKET HOLE.

CAUTION: STATIC SENSITIVE DEVICE FOLLOW PROPER E.S.D. HANDLING PROCEDURES WHEN WORKING WITH THIS PART.



*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= +DECIMAL PRECISION MAX.= +0.00 -DECIMAL PRECI LINICONITONII ED DOCLINIENT



290 E. HELEN ROAD PALATINE, IL 60067-6976 PHONE: +1.847.359.2790

FAX: +1.847.359.6538 WEB: WWW.LUMEX.COM

1.0mm X 0.5mm SURFACE MOUNT LED, 525nm ULTRA PURE GREEN, WATER CLEAR LENS, TAPE AND REEL.

KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

THE SPECIFICATIONS MAY CHANGE AT ANY TIME WITHOUT NOTICE DUE TO NEW MATERIALS OR PRODUCT IMPROVEMENT. CONFIDENTIAL INFORMATION
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL

CISION DIVED DIVITABLE DI DOCUMENT							
	DATE:	7.12.10	DRAWN BY:	MP			
	PAGE:	1 OF 1	CHKD BY:	KF			
	SCALE:	N/A	APRVD BY:	SS			
	UNIT: mm [INCH]		® C				
-							