



LOC		DIST		REVISIONS			
A	1	P	LTH	DESCRIPTION	DATE	OWN	APVD
				SEESHEET 1 OF 2			

POSITIONS Polzahl	n	a±0.2	b	c	d <sub>-0.2</sub>	e <sub>-0.25</sub>	f	CODING Kodierung	CAVITY NUMBERING Kammerbezeichnung	ORDER NO. REV. Bestell-Nr.	ORDER NO. REV. Bestell-Nr.	WEIGHT Gewicht	POS.	QTY Stueck	DESCRIPTION Benennung Einzelteil	MATERIAL Werkstoff	FINISH Oberflaeche	COLOUR/ Farbe
21	6	38.5	30	45	42.5	38.5	36.5	B (GROOVES) Nuten A-C		5-966140-6 A	4-966140-6 A	18.3g	4	7	TAB (43.4mm)	CuSn0.15/0.20	SEL. SILVER PLATED	
										6-966140-6 C	3-966140-6 C		3	7	TAB (34.4mm)	CuSn0.15/0.20	SEL. SILVER PLATED	
18	5	33.5	25	40	37.5	33.5	31.5	A (GROOVES B-C) (Nuten B-C)		6-966140-1 C	3-966140-1 C	16.0g	2	7	TAB (25.4mm)	CuSn0.15/0.20	SEL. SILVER PLATED	
										4	6		TAB (43.4mm)	CuSn4	SEL. SILVER PLATED			
15	4	28.5	20	35	32.5	28.5	26.5	A (GROOVES B-C) (Nuten B-C)		6-966140-2 C	3-966140-2 C	13.6g	3	7	TAB (34.4mm)	CuSn4	SEL. SILVER PLATED	
										2	7		TAB (25.4mm)	CuSn4	SEL. SILVER PLATED			
12	3	23.5	15	30	27.5	23.5	21.5	A (GROOVES B-C) (Nuten B-C)		6-966140-3 C	3-966140-3 C	11.2g	1	1	21 POS. HOUSING	PA66-GF13	BLACK/schwarz	
										4	6		TAB (43.4mm)	CuSn4	SEL. SILVER PLATED			
9	2	18.5	10	25	22.5	18.5	16.5	A (GROOVES B-C) (Nuten B-C)		6-966140-4 C	3-966140-4 C	8.9g	3	6	TAB (34.4mm)	CuSn4	SEL. SILVER PLATED	
										2	6		TAB (25.4mm)	CuSn4	SEL. SILVER PLATED			
6	1	13.5	5	20	17.5	13.5	11.5	A (GROOVES B-C) (Nuten B-C)		6-966140-5 C	3-966140-5 C	6.6g	4	5	TAB (43.4mm)	CuSn4	SEL. SILVER PLATED	
										3	5		TAB (34.4mm)	CuSn4	SEL. SILVER PLATED			
													1	1	18 POS. HOUSING	PA66-GF13	BLACK/schwarz	
													4	2	TAB (43.4mm)	CuSn4	SEL. SILVER PLATED	
													3	2	TAB (34.4mm)	CuSn4	SEL. SILVER PLATED	
													2	2	TAB (25.4mm)	CuSn4	SEL. SILVER PLATED	
													1	1	6 POS. HOUSING	PA66-GF13	BLACK/schwarz	

POSITIONS Polzahl	n	a±0.2	b	c	d <sub>-0.2</sub>	e <sub>-0.25</sub>	f	CODING Kodierung	CAVITY NUMBERING Kammerbezeichnung	ORDER NO. REV. Bestell-Nr.	ORDER NO. REV. Bestell-Nr.	WEIGHT Gewicht	POS.	QTY Stueck	DESCRIPTION Benennung Einzelteil	MATERIAL Werkstoff	FINISH Oberflaeche	COLOUR/ Farbe
21	6	38.5	30	45	42.5	38.5	36.5	B (GROOVES) Nuten A-C		8-966140-6 A	1-966140-6 A	18.3g	4	7	TAB (43.4mm)	CuSn4	TINNED/verzinkt	
										9-966140-6 F	966140-6 F		3	7	TAB (34.4mm)	CuSn4	TINNED/verzinkt	
18	5	33.5	25	40	37.5	33.5	31.5	A (GROOVES B-C) (Nuten B-C)		9-966140-1 F	966140-1 F	16.0g	2	7	TAB (25.4mm)	CuSn4	TINNED/verzinkt	
										1	1		21 POS. HOUSING	PA66-GF13	BLACK/schwarz			
15	4	28.5	20	35	32.5	28.5	26.5	A (GROOVES B-C) (Nuten B-C)		9-966140-2 F	966140-2 F	13.6g	4	6	TAB (43.4mm)	CuSn4	TINNED/verzinkt	
										3	6		TAB (34.4mm)	CuSn4	TINNED/verzinkt			
12	3	23.5	15	30	27.5	23.5	21.5	B (GROOVES) Nuten A-C		8-966140-3 A	1-966140-3 A	11.2g	2	6	TAB (25.4mm)	CuSn4	TINNED/verzinkt	
										5	1		12 POS. HOUSING	PA66-GF13	NATURAL/natur			
9	2	18.5	10	25	22.5	18.5	16.5	A (GROOVES B-C) (Nuten B-C)		9-966140-3 F	966140-3 F	11.2g	4	4	TAB (43.4mm)	CuSn4	TINNED/verzinkt	
										3	4		TAB (34.4mm)	CuSn4	TINNED/verzinkt			
6	1	13.5	5	20	17.5	13.5	11.5	A (GROOVES B-C) (Nuten B-C)		9-966140-4 F	966140-4 F	8.9g	2	4	TAB (25.4mm)	CuSn4	TINNED/verzinkt	
										1	1		12 POS. HOUSING	PA66-GF13	BLACK/schwarz			
										9-966140-5 F	966140-5 F	6.6g	4	3	TAB (43.4mm)	CuSn4	TINNED/verzinkt	
										3	3		TAB (34.4mm)	CuSn4	TINNED/verzinkt			
													2	3	TAB (25.4mm)	CuSn4	TINNED/verzinkt	
													1	1	9 POS. HOUSING	PA66-GF13	BLACK/schwarz	
													4	2	TAB (43.4mm)	CuSn4	TINNED/verzinkt	
													3	2	TAB (34.4mm)	CuSn4	TINNED/verzinkt	
													2	2	TAB (25.4mm)	CuSn4	TINNED/verzinkt	
													1	1	6 POS. HOUSING	PA66-GF13	BLACK/schwarz	

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm. TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±, 1 PLC ±, 2 PLC ±, 3 PLC ±, 4 PLC ±, ANGLES ±0.2°. MATERIAL: SEE PARTS LIST. FINISH: SEE PARTS LIST.

OWN: Mahlike, B. 160CT2014  
 CHK: Krauss, S. 170CT2014  
 APVD: Goepfel, C. 200CT2014  
 PRODUCT SPEC: -  
 APPLICATION SPEC: -

**STE** TE Connectivity  
 NAME: TAB HEADER, 2.8x0.8, 6-21 POS. Messerleiste, 2.8x0.8, 6-21 pol.  
 SIZE: A1 CAGE CODE: 00779 DRAWING NO: C=966140  
 WEIGHT: - RESTRICTED TO: -  
 Customer Drawing SCALE: 2:1 SHEET: 2 OF 2 REV: F7