









17	OBSOLETE		$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	NO	FULLY LOADED	 1-213574-7
17	OBSOLETE		$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	NO		1-213574-6
17	OBSOLETE		$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	YES		1-213574-5
17	OBSOLETE		$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	YES		1-213574-4
17	OBSOLETE		$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	YES		1-213574-3
17	OBSOLETE		$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	YES		1-213574-2
17	OBSOLETE		$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	YES	FULLY LOADED	1-213574-1
			$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	NO	FULLY LOADED	1-213574-0
17	OBSOLETE		$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	NO		213574-9
17	OBSOLETE		$\frac{8.38}{.330}$	$\frac{8.38}{.330}$	YES		213574-8
17	OBSOLETE		$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	YES		213574-7
17	OBSOLETE		$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	YES		213574-6
	OBSOLETE	—	$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	NO	FULLY LOADED	213574-5
17	OBSOLETE		$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	YES		213574-4
	OBSOLETE	—	$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	YES		213574-3
			$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	YES	FULLY LOADED	213574-2
	OBSOLETE	—	$\frac{8.81}{.347}$	$\frac{8.81}{.347}$	YES		213574-1
CONTACT/BOARD LOCK POSITION			ZZ	YY	DIMPLE	CIRCUIT CAVITIES LOADED	PART NUMBER

RECOMMENDED PC BOARD LAYOUT
SCALE 4:1
57 [.062] PC BOARD THICKNESS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN C RICHARD OK 11/27/89 12-4-89 R.STONE		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± ± 0.25 [0.010] 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME CONNECTOR ASSEMBLY, SOCKET, 34 POSITION, RIGHT ANGLE, WITH BOARDLOCKS, M SERIES	
		PRODUCT SPEC APPLICATION SPEC		SIZE A1 00779	
MATERIAL: HOUSING:  HARDWARE:  CONTACT:  LOCATION:  WATER: 		WEIGHT —		DRAWING NO C=213574	
FINISH HARDWARE:  CONTACT:  LOCATION:  WATER: 		CUSTOMER DRAWING		SCALE: 2:1 SHEET 1 of 1 REV V2	