



SHELL SIZE	LAYOUT	Ø A	B MINI	CAPACITY C		HEXAGON D	E MAX
				STANDARD	REDUCING SEAL		
14	SEE NOTE 4	34.60	70	7.00/14.00	5.00/12.00	26.00	36.70
12	SEE NOTE 4	29.70	65.5	5.00 / 12.00	3.00 / 9.00	24.00	32.70
10	SEE NOTE 4	26.20	62	2.50 / 8.00	1.50 / 5.00	18.50	29

FEMALE CONNECTOR
(detail 1)



MATERIAL :


Coupling Nut:Polyamid UL94 V-0
Inset:Polyamid UL94 V0
Backshell body :Polyamid UL94 V-0
Backshell nut:Polyamid UL94 V-0
Shell : Polyamid UL94 V-0
Coupling spring : Stainless steel
O'seal : Nitril

PERFORMANCE CHARACTERISTICS :

Operating temperature:-40°C up to 105°C
Insulation resistance:5000 MΩmin
Test potential:2000 Vrms for #16 layout and 1500Vrms for #20 layout
Corrosion salt spray:500 hours
Durability:250 matings and unmatings
Sealing in mated conditions:
-IP68 1 bar during 1 week : immersion under 10 m of water. (IEC 60529)
-IP69K : exposure to high pressure water of cleaning equipment(DIN 40050)

NOTES :

- 1-Plug,backshell and the reducing seal are delivered as a kit
The backshell already includes the standard seal.
- 2-Contact to be ordered separately :refer to TRIM TRIO catalog
- 3-Colored ring to be order separately refer to customer drawing C006-UTSI-A
- 4-developed Grommet arrangements : refer to C042-UTSI-A
- 5- for wirering instructions, refer to BT214



CUSTOMER DRAWING

C	05/02/08	--	Add shell size 12 and 14	--
ISS	DATE	Latest modification - by: RAGINE M.		MOD N°
Designed by:		RAGINE M. Date:07/06/07		CUSTOMER DRAWING
TITLE		CABLE PLUG + GROMMET BACKSHELL UTS CONNECTOR		
Scale	2/1		General linear Tolerances: ±0.1	NPRDS / PROJECT UTSI
		WWW.SOURIAU.COM		This document is the property of SOURIAU It must not be reproduced or communicated without permission
FORMAT	A2	SOURIAU DRG N° CO27-UTSI-A		SHEET 1 / 1