



DWG. NO. S99615		BILL OF MATERIAL	
ITEM	PART NO.	DESCRIPTION	QTY.
1	UTS718A2M3NPT1	UTS RECEPTACLE	1
2	UT018SEAL68S	SEAL	1
3	23-003110	WASHER, RUBBER	1

CIRCUIT	MAXIMUM CURRENT (AMP)	MAXIMUM WIRE Ø (mm)
2,4	44	6.3
1,3,5	13	3.3

NOTES:

- MATES WITH UTS6\_\_18X2M3P.
- CIRCUITS 2 & 4 USE 3.6mm SOCKET CONTACTS ORDERED SEPARATELY. SEE SOURIAU BSD 202333001 FOR CONTACT OPTIONS.
- CIRCUITS 1, 3 AND 5 USE 1.6mm SOCKET CONTACTS ORDERED SEPARATELY. SEE SOURIAU SD61512 FOR CONTACT OPTIONS.
- MATERIALS: ALL ROHS COMPLIANT
  - RECEPTACLE SHELL: POLYAMIDE UL94VO, COLOR-BLACK.
- MECHANICAL / ENVIRONMENTAL PERFORMANCE
  - OPERATING TEMPERATURE: -40° TO +105°C.
  - CORROSION: SALT SPRAY, 500 HOURS.
  - DURABILITY: 250 MATE-UNMATE CYCLES.
  - VIBRATION: SINUSOIDAL PER CEI 60512-4; 10-TO-2,000 Hz.
  - THERMAL SHOCK: 5 CYCLES X 30-MINUTES: -40° TO +105°C.
  - SEALING IN MATED CONDITION: IEC 60529-IP68: 10M WATER, 1-WEEK; DYNAMIC-IP69K: HIGH-PRESSURE WATER, DIN 40050.
- ELECTRICAL PERFORMANCE
  - DIELECTRIC WITHSTANDING VOLTAGE / INSULATION RESISTANCE 2200 VRMS MAX. BETWEEN CIRCUITS / 5000 M Ohm MIN. @ 500 VDC.
  - OPERATING VOLTAGE: 600 VAC MAX.
- PACKAGING: SOURIAU LABEL ON BULK PACKAGE INCLUDES PART NO. & QTY. RUBBER WASHER IS SOLD SEPARATELY.
- UL 1977 RECOGNIZED
- POWER CONTACT RESISTANCE: <= 0.9 Milli Ohm. SIGNAL CONTACT RESISTANCE: <= 5 Milli Ohm.
- U.S. PATENT 7,955,125.
- MOLDING VOID CORES ARE INDICATED "X".
- PANEL CUTOUT IF APPLICABLE: TAP DRILL 59/64 OR .922 IN (23.42mm) 3/4-NPT INTERNAL THREADS.
- TYPICAL INSTALLATION: OUTLET BOX. RECOMMENDED TOOLS; 8 POINT 1 1/4 SOCKET: MAX. TORQUE 66 IN-LBS.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC. IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION. CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.



Client Drawing Approval	
X	Option
	Approved with no Exceptions
	Approved with Exceptions Noted
	Revision/Resubmission Required
	Rejected
The signature above indicates the client's authorized representative has reviewed, understands, and concurs with the requirements defined herein. If no signature is provided, placement of a purchase order by the client is considered drawing acceptance.	

LINEAR MEASURE:	INCH [mm]
THIRD ANGLE PROJECTION	
TOLERANCES UNLESS OTHERWISE SPECIFIED	
No. OF PLACES	INCH [mm]
ONE PLACE	±.1 [±.3]
TWO PLACES	±0.02 [±.5]
THREE PLACES	±0.010 [±.25]
ANGLES	±1°

DRAWING TITLE	
<b>UTS RECEPTACLE, SIZE-18, SOCKET, NPT THREADS</b>	
CAT NO.	<b>UTS718X2M3S</b>
CAGE NO: 09922	SIZE: B
<b>CUSTOMER</b>	
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.	<a href="http://www.souriau.com">www.souriau.com</a>
APPROVAL	DRAWN: RKO 03-15-11 CHKD : NPP 03-15-11 DSGN : NPP 03-15-11 MFG : DH 03-15-11 QC : BB 03-15-11 DRAWING SCALE: 2:1 DRAWING NO. S99615 REV B
	1 OF 1

B

A

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.