




THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	22APR2015	DL	CW

Ø 3.2
(2PL)

22
30

PANNEL CUT OUT

NOTES:
1. TECHNICAL CHARACTERISTICS:
BODY MATERIAL: DIE CAST ZINC ALLOY
SURFACE TREATMENT: NI PLATED
OPERATION TEMPERATURE: -40-+125°C
DEGREE OF PROTECTION: IP65 (MATED)

注释:
1. 技术参数:
主体材料: 锌合金
表面处理: 镀镍
工作温度: -40-+125°C
防护等级: IP65(配合)

T1506033000-000

H3A-MAG-EMC

ASSEMBLY PART
NUMBER

ASSEMBLY PART
DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 22APR2015

DAVID LI

CHK 22APR2015

CHRIS WANG

APVD 22APR2015

XU XIANG

PRODUCT SPEC

108-137012

APPLICATION SPEC


114-137012

WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:
mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL

-

FINISH

-

TE

TE Connectivity

NAME
H3A-MAG-EMC

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 - T1506033000000 -

SCALE 3:2 SHEET 1 OF 1 REV A