


THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO US IN CASE OF NO USAGE

REV.	DATE	DESCRIPTION	BY	C 'K 'D '
01	03/06/97	CRIMP TOOL ADDED	K.N.	
02	04/15/03	ADD WIRE SIZE INFORMATION	R.Ch	
03	05/05/09	ADD D28 PROTECTION	R.Ch	



- CURRENT RATING : 13 A MAX.
- CONTACT RESISTANCE : $\leq 3 \text{ m Ohm}$
- CONTACT RETENTION IN INSERT : 110 N MIN.


- MS-M
- UT-BANTAM
- UTP-BANTAM
- METALOK BANTAM
- SMS QIKMATE

CRIMP TOOL : AF8 TOOL WITH LOCATOR TP1142 (SELECTOR 8)

WIRE SIZE : AWG 16-14
1.50 - 2.50 mm²

- CONTACT BODY :
MATERIAL : BRASS
*PLATING : T : 5 μ TIN ALL-OVER, OVER 2 μ NICKEL MIN. ALL-OVER
K, J : GOLD FLASH ALL-OVER, OVER 2 μ NICKEL MIN. ALL-OVER
- CONTACT INNER SPRING :
MATERIAL : BERYLLIUM COPPER
*PLATING : D28 : 0.75 μ MIN. GOLD ALL-OVER, OVER 2 μ NICKEL MIN. ALL-OVER
K : 0.4 μ MIN. GOLD ALL-OVER, OVER 2 μ NICKEL MIN. ALL-OVER
J : GOLD FLASH ALL-OVER, OVER 2 μ NICKEL MIN. ALL-OVER
T : 5 μ TIN ALL-OVER, OVER 2 μ NICKEL MIN. ALL-OVER
- RETAINING SPRING :
MATERIAL : BERYLLIUM COPPER - UNPLATED

GEN. ST.	01	02	03	04	05	06	07	08	0D	50	60	70	80	90		
INT. ST.	10 11	12 13	14 18	20 31	32 33	34 38	39 40	42 43	44 45	46 48	56 70	72 73	75 76	81 82	83 84	88

1DEC ±0,2 1DEC 2DEC ±0,1 2DEC ANGLES ±1° HOEKEN	APPR. DRAFT CHECKED	DATE 20-11-95	SIGN. K.NIETVELT	MS HYFEN FEMALE CRIMP CONTACT-AWG14 CAT. No . RC 14M30*
WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.	PROD. MGR. PR.ENG.MGR. PR.MGT.MGR.			 SOURIAU Connection Technology SOURIAU Route Nationale 23 72470 CHAMPAGNE SCALE
ALL DIMENSIONS IN MM 	REFERENCES / REFERENTIES BS, A, 200014, 002 EPM 187 BP, D, 202021, 001			BS, A , 202060, 001, 03 DRAWING NR CUSTOMER DRAWING
ALL AFMETINGEN IN MM				