







注記
NOTES.

- △1. 公差非累積
NON CUMULATIVE TOLERANCE
2. 推奨基板厚 : $t=1.6\pm0.2$
RECOMMENDED P.C.B. THICKNESS : $t=1.6\pm0.2$
△3. ターミナル メッキ仕様
TERMINAL PLATING
金メッキ : $0.3\text{ }\mu\text{m MIN.}$ (接点部)
GOLD : $0.3\text{ }\mu\text{m MIN.}$ (CONTACT AREA)
錫メッキ : $1.0\text{ }\mu\text{m MIN.}$ (半田付け部)
TIN : $1.0\text{ }\mu\text{m MIN.}$ (SOLDER AREA)
ニッケルメッキ : $2.0\text{ }\mu\text{m MIN.}$ (下地メッキ)
NICKEL : $2.0\text{ }\mu\text{m MIN.}$ (UNDER PLATING)
4. 本製品は 52986-**71 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 52986-**71.



パネル取り付け穴推奨寸法
RECOMMENDED PANEL OPENING



33.02	54.52	57.93	54.03	63.83	46.91	41.91	52986-***79	52986-6879	68
27.79	43.09	46.5	42.6	52.4	35.48	30.48		52986-5079	50
12.7	34.20	37.61	33.71	43.51	26.59	21.59		↑ -3679	36
12.55	27.85	31.26	27.36	37.16	20.24	15.24		-2679	26
→ 24.04	27.45	23.55	33.35	16.43	11.43			↓ -2079	20
→ 20.23	23.64	19.74	29.54	12.62	7.62			52986-1479	14
G	F	E	D	C	B	A	MODEL NO.	製品番号 MODEL NO.	極数 CKT

REVISED	EC NO: J2007-1900	2007/02/02	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC		THIRD ANGLE PROJECTION	MATERIAL NO.	QTY.	
	DRWNSAI T001	2007/02/05		10 UNDER	± 0.2	DRAWN BY HKAWABAT	DATE '04/05/18	TITLE 1.27 I/O METAL/L R/A REC ASSY (CLAMP) -LEAD FREE-						
	CHKDKK TOYODA	2007/02/05		10 OVER 30 UNDER	± 0.25	CHECKED BY KTOJO	DATE '04/05/18							
	APPR:NUKITA	2007/02/05		30 OVER	± 0.3	APPROVED BY MSASAO	DATE '04/05/18	MOLEX MOLEX INCORPORATED						
				ANGULAR ±3 °	MATERIAL NO.		DOCUMENT NO.		SHEET NO.					
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SEE CHART		SD-52986-020		1 OF 2					
			REV			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

10 9 8 7 6 5 4 3 2 1

F










E

D

C

B

A



14 極の場合

IN CASE OF 14 CKT.

20 極の場合


IN CASE OF 20 CKT.

26,36,50,68 極の場合

IN CASE OF 26,36,50,68 CKT.

シェルロック位置及びハウジングフード形状

SHAPE OF SHELL LOCK AND HS'G HOOD.



基板穴推奨寸法 (部品実装側)
RECOMMENDED P.C.B. LAYOUT (COMPONENT SIDE)

REVISED EC NO: J2007-1900 DRW:KSAIT001 CHKD:KTOY00A APPR:NUKITA	2007/02/02 2007/02/05 2007/02/05	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
			10 UNDER	± 0.2	DRAWN BY HKAWABAT	DATE ' 04/05/18	TITLE 1.27 I/O METAL/L R/A REC ASSY(CLAMP) -LEAD FREE-			
			10 OVER 30 UNDER	± 0.25	CHECKED BY KT0JO	DATE ' 04/05/18				
			30 OVER	± 0.3	APPROVED BY MSASAO	DATE ' 04/05/18	MOLEX MOLEX INCORPORATED			
			ANGULAR ±3 °		MATERIAL NO.					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-52986-020		2 OF 2	
REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						