
A Dimensions: [mm]












Scale - 3:1

Reference on drawing	Description				
•	Start of winding				
Marking	101 (Inductance Code)				

B Recommended land pattern: [mm]



Scale - 5:1

D Electrical Properties:

Properties	Test conditions		Value	Unit	Tol.
Inductance	100 kHz/ 1 V	L	100	μΗ	±20%
Rated current	ΔT = 40 K	I _R	0.70	А	max.
Saturation current	IΔL/LI < 30%	I _{sat}	0.71	А	typ.
DC Resistance	@ 20°C	R _{DC}	500	mΩ	±30%
Self resonant frequency		f _{res}	8.8	MHz	typ.

C Schematic:



E General information:

It is recommended that the temperature of the part does not exceed 125°C under worst case operating conditions.

- •Ambient temperature: -40°C to +85°C (refering to I_R)
- •Operating temperature: -40°C to +125°C
- •Storage temperature (on tape & reel): -20°C to +60°C; 75% RH max.
- •Test conditions of Electrical Properties: 20°C, 33% RH if not specified differently

				Projection ————————————————————————————————————
				Würth Elektronik eiSos
1.3	2015-05-18	SSt	JRS	EMC & Inductive Solution Max-Eyth-Str. 1
1.2	2014-09-08	SSt	JRS	74638 Waldenburg
1.1	2014-06-12	SSt	SSt	Germany Tel. +49 (0) 79 42 945
1.0	2014-02-03	SSt	JRS	www.we-online.com eiSos@we-online.com
REV	DATE	BY	CHECKED	0.0000000000000000000000000000000000000



Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com

DESCRIPTION

WE-LQS SMD Power Inductor

Order.- No.

Size: 6028

74404063101




SIZE A4


This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment only. This product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik eiSos GmbH & Co KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, strip control), transportation (automotive control, train control, strip control), transportation (automotive control, train control, strip control), transportation (automotive control, train control, trai the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.



F1 Typical Inductance vs. Current Characteristics:




F2 Typical Impedance Characteristics:



				Projection -	WE-LQS SMD Power Inductor
1.3	2015-05-18	SSt	JRS	Würth Elektronik eiSos GmbH & Co. I EMC & Inductive Solutions	
1.2	2014-09-08	SSt	JRS	Max-Eyth-Str. 1 74638 Waldenburg	Order No.
1.1	2014-06-12	SSt	SSt	Germany Tel. +49 (0) 79 42 945 - 0	ROHS&REACh
1.0	2014-02-03	SSt	JRS	www.we-online.com eiSos@we-online.com	74404063101 WORTH ELEKTRONIK A4
REV	DATE	BY	CHECKED	GIGGGGWG GIIIIIG.GGIII	Size: 6028


G Packaging Specification - Tape and Reel [mm]:



sectional drawing A-A





		Α0	В0	w	P1	т	T1	Т2	K0	D0	D1	E1	E2	F	P0	P2	Tape	VPE / packaging unit
	tolerance	typ.	typ.	±0,3	±0,1	max.	min.	ref.	typ.	+0,1	min.	±0,1	min.	±0,05	±0,1	±0,05		pcs.
	5020	5,40	5,40	12,00	8,00	0,60	0,10	2,50	2,20	1,50	1,50	1,75	10,25	5,50	4,00	2,00	Polystyrene	2500
l o	5040	5,30	5,30	12,00	8,00	0,60	0,10	4,50	4,20	1,50	1,50	1,75	10,25	5,50	4,00	2,00	Polystyrene	1500
Size	6028	6,40	6,40	16,00	12,00	0,60	0,10	3,60	3,30	1,50	1,50	1,75	14,25	7,50	4,00	2,00	Polystyrene	2000
"	6045	6,40	6,40	16,00	12,00	0,60	0,10	5,00	4,70	1,50	1,50	1,75	14,25	7,50	4,00	2,00	Polystyrene	1500
	8040	8,35	8,35	16,00	12,00	0,60	0,10	4,70	4,40	1,50	1,50	1,75	14,25	7,50	4,00	2,00	Polystyrene	1000







sectional drawing B-B





		Α	В	С	D	N	W1	W2	W3	W3
tolerar	nce	± 2,0	min.	± 0,8	min.	min.	+ 2	max.	min.	max.
Tape width	12 mm	330,00	1,50	13,00	20,20	60,00	12,40	18,40	11,90	15,40
rape width	16 mm	330,00	1,50	13,00	20,20	60,00	16,40	22,40	15,90	19,40





| Pull-of force | | Tape width | | 12 mm | 0,1 N - 1,3 N | 16 mm | 0,1 N - 1,3 N |

	1.3	2015-05-18	SSt	JRS	
	1.2	2014-09-08	SSt	JRS	
	1.1	2014-06-12	SSt	SSt	
1	1.0	2014-02-03	SSt	JRS	
_	REV	DATE	BY	CHECKED	



eiSos@we-online.com

Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com DESCRIPTION

WE-LQS SMD Power Inductor

Order.- No.

Size: 6028

74404063101

COMPLIANT ROHS&REACH WÜRTH ELEKTRONIK

A4


SIZE

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and reliability standard and reliability standard and reliability standard is especially required or where a failure of the products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation signal, disaster prevention, medical, public information network etc.. Würth Elektronik eSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

H Soldering Specifications:



H1: Classification Reflow Profile for SMT components:



H2: Classification Reflow Profiles

Profile Feature	Pb-Free Assembly	
Preheat - Temperature Min (T _{smin}) - Temperature Max (T _{smax}) - Time (t _s) from (T _{smin} to T _{smax})	150°C 200°C 60-120 seconds	
Ramp-up rate (T _L to T _P)	3°C/ second max.	
Liquidous temperature (T_L) Time (t_L) maintained above T_L	217°C 60-150 seconds	
Peak package body temperature (Tp)	See Table H3	
Time within 5°C of actual peak temperature (tp)	20-30 seconds	
Ramp-down rate (T _P to T _L)	6°C/ second max.	
Time 25°C to peak temperature	8 minutes max.	

refer to IPC/JEDEC J-STD-020D

H3: Package Classification Reflow Temperature

	Package Thickness	Volume mm³ <350	Volume mm³ 350 - 2000	Volume mm³ >2000
PB-Free Assembly	< 1.6 mm	260°C	260°C	260°C
PB-Free Assembly	1.6 - 2.5 mm	260°C	250°C	245°C
PB-Free Assembly	≥ 2.5 mm	250°C	245°C	245°C

refer to IPC/JEDEC J-STD-020D

				Projection -		DESCRIPTION WE-LQS SMD PO	ower Inductor	
1.3	2015-05-18	SSt	JRS	Würth Elektronik eiSos Gmbl- EMC & Inductive Solutions Max-Eyth-Str. 1	1 & Co. KG	WE-LQS SIVID PO	Jwei illuuctoi	
1.2	2014-09-08	SSt	JRS	74638 Waldenburg		Order No.	COMPLIANT	SIZE
1.1	2014-06-12	SSt	SSt	Germany Tel. +49 (0) 79 42 945 - 0		- 4404000404	ROHS&REACH	OIZE
1.0	2014-02-03	SSt	JRS	www.we-online.com eiSos@we-online.com		74404063101	WONTH ELEKTRONIK	A4
REV	DATE	BY	CHECKED	CIOCOSSIVE GIIIIIE.COIII		Size: 6028		

I Cautions and Warnings:

The following conditions apply to all goods within the product series of WE-LQS of Würth Elektronik eiSos GmbH & Co. KG:

General:

All recommendations according to the general technical specifications of the data sheet have to be complied with.

The usage and operation of the product within ambient conditions, which probably alloy or harm the wire isolation, has to be avoided.

If the product is potted in customer applications, the potting material might shrink during and after hardening. The product is exposed to the pressure of the potting material with the effect that the core, wire and termination is possibly damaged by this pressure and so the electrical as well as the mechanical characteristics are endangered to be affected. After the potting material is cured, the core, wire and termination of the product have to be checked if any reduced electrical or mechanical functions or destructions have occurred.

The responsibility for the applicability of customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products do also apply to customer specific products.

Cleaning agents that are used to clean the customer application might damage or change the characteristics of the component, body, pins or termination.

Direct mechanical impact to the product shall be prevented as the core material could flake or in worst case it could break.

Product specific:

Follow all instructions mentioned in the data sheet, especially:

- •The soldering profile has to be complied with according to the technical reflow soldering specification, otherwise this will void the warranty.
- •All products shall be used before the end of the period of 12 months based on the product date code, if not a 100% solderability can't be ensured.
- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.

The general and product specific cautions comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable; however, no responsibility is assumed for inaccuracies or incompleteness.



				Projection		DESCRIPTION		
				+		 WE-LQS SMD Po	wor Industor	
				Würth Elektronik eiSos Gmbł	<u>I</u> Н & Co. KG	WE-LQ3 SIVID PO	JWGI IIIUUGIOI	
1.3	2015-05-18	SSt	JRS	EMC & Inductive Solutions Max-Eyth-Str. 1				
1.2	2014-09-08	SSt	JRS	74638 Waldenburg		Order No.	COMPLIANT	SIZE
1.1	2014-06-12	SSt	SSt	Germany Tel. +49 (0) 79 42 945 - 0		74404000404	ROHS&REACH WÜRTH ELEKTRONIK	0.22
1.0	2014-02-03	SSt	JRS	www.we-online.com eiSos@we-online.com		74404063101	The state of the s	A4
REV	DATE	BY	CHECKED	CIOCOSSWC CHIIIIC.COM		Size: 6028		

J Important Notes:

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications.

In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component.

Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.



6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered.

The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG.

Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

				Projection ————————————————————————————————————		DESCRIPTION			
				7)	11.8.02.1/0	WE-LQS SMD Power Inductor			
1.3	2015-05-18	SSt	JRS	Würth Elektronik eiSos Gmbł EMC & Inductive Solutions Max-Eyth-Str. 1	H & CO. KG				
1.2	2014-09-08	SSt	JRS	74638 Waldenburg		Order No.	COMPLIANT	SIZE	
1.1	2014-06-12	SSt	SSt	Germany Tel. +49 (0) 79 42 945 - 0		74404000404	ROHS&REACH	OIZE	
1.0	2014-02-03	SSt	JRS	www.we-online.com eiSos@we-online.com		74404063101		A4	
REV	DATE	BY	CHECKED	CIOO3®WC OHIIIIC.COM		Size: 6028			