

5

4

3

2

1

DRAWING NO.

CPMC8810-CUST

REVISIONS

OFFICAL RELEASE

01

03-05-09

Z G B Y T

Thomas Chow

Description: Stright BNC Crimp Plug For RG59 Plenum Cable

Part No: CPMC8810

Application: For Cable RG59 Plenum

Crimp Tool: 24-9958P

Impedance: 50 Ohms


Fequency Range: 0-4 GHz

Material:

Body	Zinc	Nickel Plated
Contact	Brass	Gold Plated
Insulator	PTFE	
Crimp Sleeve	Brass	Nickel Plated
Coupling Nut	Zinc	Nickel Plated

RoHS Compliance: Yes

Technical Detail: Refer to Emerson Document P/N 27-0000



**DIM OUTLINE**

**CUSTOMER COPY**

受控 CONTROLLED DOCUMENT					
编号 P/N	CPMC8810-CUST	版本 Rev	01	日期 Rel'd Date	Apr29,09

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
		GARY.ZHG	03-05-09
DECIMALS	mm	CHECKED BY	DATE
X	± 0.5	TERRY.W	03-05-09
X.X	± 0.3	APPROVED BY	DATE
X.XX	± 0.1	THOMAS	03-10-09
ANGLES	± 0.5°	U/M	mm

 <b>cinch</b> CONNECTIVITY SOLUTIONS <small>a bel group</small>		TITLE	
		STRAIGHT BNC CRIMP PLUG FOR R59 PLENUM CABLE	

THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.			SHEET 1 OF 1	DRAWING NO. CPMC8810-CUST	SIZE A
---	--	--	--------------	---------------------------	--------

5

4

3

2

1