



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
HOUSING	TPE	SEE TABLE
RIVET	BRASS	
CONTACT	BRASS	
CAGE	NYLON	BLACK



CATALOG NO. HBLFRSBK
(NOT SHOWN TO SCALE)

- NOTES:
- DIMENSIONS ARE IN INCHES ± .02
[mm] ± .5
 - RATING : 600VAC/250VDC 400 AMP.
 - UL/c-UL ENCLOSURE TYPES 3R, 4X, 12,
SEE INSTRUCTION SHEET.

HUBBELL CAT. NO.	COLOR
HBLFRSBK	BLACK
HBLFRSW	WHITE
HBLFRSGN	GREEN
HBLFRSR	RED
HBLFRSBL	BLUE
HBLFRSO	ORANGE
HBLFRSBN	BROWN
HBLFRSY	YELLOW

3	REDRAWN WITH EMBEDDED CAD MODEL WITH NO CHANGES TO PART GEOMETRY. PER DCN 21895 SPN	DJP APP	2/5/16 DATE
REV	DESCRIPTION	APP	DATE
THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE			
TITLE SINGLE POLE FEMALE RECEPTACLE W/STUD			
TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
.XX = ± .01 .XXX = ± .005 ANGLES = ± 2°		DR. BY MJM	APP. BY
		TR. BY	SCALE 1:1
		CHK. BY	DATE 6/11/03