


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	DRAWING REPLACES WPHD15CA-OD1 AT REV B	12/1/14	D. CASTRO



NOTES:

1. WALL PLATE MATERIAL: STAINLESS STEEL
2. SPECIFICATIONS
 - 2.1 CABLE:
 - U.L. STYLE 2919
 - CONDUCTORS: FIVE MINIATURE 75Ω COAXIAL
 - SHIELDING: ALUMINIZED MYLAR AND COPPER BRAID
 - JACKET: GRAY PVC
 - 2.2 D-SUB CONNECTOR
 - INSULATOR: UL94V-0 THERMOPLASTIC
 - CONTACTS: GOLD PLATED
 - SHELL: TIN FINISH
 - HOOD: GRAY PVC
 - HARDWARE: 4-40UNC
 - 2.3 BNC
 - SHELL: NICKEL PLATED BRASS
 - CONTACTS: GOLD PLATED BRASS
 - INSULATOR: DELRIN
 - CHARACTERISTIC IMPEDANCE: 75Ω
 - STRAIN RELIEF: GRAY PVC
3. ALL BNC SHIELDS ELECTRICALLY TIED TO HDB15F SHELL.
4. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
5. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU (RoHS DIRECTIVE)



WIRE MAP	
J1	BNC JACKS
PIN 1	J2
PIN 2	J3
PIN 3	J4
PIN 4	N/C
PIN 5	SHIELD
PIN 6	SHIELD
PIN 7	SHIELD
PIN 8	SHIELD
PIN 9	N/C
PIN 10	SHIELD
PIN 11	N/C
PIN 12	N/C
PIN 13	J6
PIN 14	J5
PIN 15	N/C
SHELL	SHIELD

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS DRAWN BY B.MAZEJKA 09/25/2003		DATE 09/25/2003		 NORTH ANDOVER, MA 01845	
OVERALL CABLE LENGTH TOLERANCE: $\leq 12 [305] = +1 [25] / -0$ $> 12 [305] \leq 60 [1524] = +2 [51] / -0$ $> 60 [1524] \leq 120 [3048] = +4 [102] / -0$ $> 120 [3048] \leq 300 [7620] = +6 [152] / -0$ $> 300 [7620] = +5\% / -0\%$		CHECKED BY D.PARHAM 09/26/2003		CATEGORY AUDIO/VIDEO			
ALL OTHER DIMENSIONAL TOLERANCES: $.X = \pm 2 [5.08]$ $.XX = \pm 0.2 [5.1]$ $.XXX = \pm .005 [13]$		APPROVED BY C.McCORMICK 09/26/2003		PRODUCT DESCRIPTION WLPLTE ASSMBLY HD15F- 5 BNC F			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE B		FSCM NO. 43321		DWG. NO. WPHD15CA	
COLOR VARIATIONS MAY OCCUR		REV. A		SCALE: 1:1.5 CAD FILE: WPHD15CA.SLDDRW		SHEET 1 OF 1	
PROJECTION 							