








DRAWING FILE NO. EA2-B0-26-610-32E-HB		REV 08-16-17
REVISIONS		
DATE	DESCRIPTION	
08-16-17	DRAWING CREATED	



BOX TYPE WIRE CONNECTORS



LOAD




PANEL CUTOUT DETAIL

TABLE A TIGHTENING TORQUE SPECIFICATIONS		
THREAD SIZE TERMINAL TYPE	WIRE SIZE	TORQUE
#6-32[M3]HARDWARE	—	7-9 IN-LBS [0.8-1.0 NM]
#10-32THD TERMINAL SCREW	ALL	15-20 IN-LBS [1.7-2.3 NM]
1/4-20THD TERMINAL SCREW	ALL	30-35 IN-LBS [3.4-4.0 NM]
#10-32 STUDS	ALL	15-20 IN-LBS [1.7-2.3 NM]
1/4-32 STUDS	ALL	30-35 IN-LBS [3.4-4.0 NM]
BOX WIRE CONNECTOR	14-10 AWG	35 IN -LBS [4.0 NM]
	8 AWG	40 IN -LBS [4.5 NM]
	6-4 AWG	45 IN -LBS [5.1 NM]
	3-1/0 AWG	50 IN -LBS [5.7 NM]

PROPRIETARY NOTICE
NOTICE TO ALL PERSONS RECEIVING THIS
DRAWING: THIS DOCUMENT IS THE PROPERTY OF
CARLING TECHNOLOGIES, INC. AND IS NOT TO BE
DISCLOSED, REPRODUCED IN WHOLE OR IN
PART OR USED FOR MANUFACTURING PURPOSES
BY ANYONE WITHOUT THE CONSENT OF
CARLING TECHNOLOGIES, INC.

DISCLAIMER
MANUFACTURER RESERVES THE RIGHT TO CHANGE
PRODUCT SPECIFICATIONS WITHOUT PRIOR NOTICE.



60 JOHNSON AVE
PLAINVILLE, CT 06062, USA
PHONE: (860) 793-9281
SALES: SALES@CARLINGTECH.COM
APPLICATION SUPPORT: TEAM2@CARLINGTECH.COM

**E-SERIES
CIRCUIT BREAKER**

DO NOT SCALE DRAWING
UNLESS OTHERWISE SPECIFIED
DIMENSIONS: IN [MM]
TOLERANCES: $\pm .020$ [0.51]

DRAWING FILE NO.
EA2-B0-26-610-32E-HB

SIZE
C

PRODUCT SERIES: E-SERIES C.B. | SHEET 1 OF 1