





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	15JUN2017	CJV	EDB




- 1 HOUSING, ORGANIZER AND CONTACT OVERMOLD: LCP, BLACK.
CONTACTS: COPPER ALLOY.
SHELL: COPPER ALLOY, NICKEL PLATED. TIN PLATED ON HOLD DOWNS.
- 2 GOLD PLATED ON MATING INTERFACE. TIN PLATED ON SOLDER TAILS.
- 3 DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
4. MINIMUM PC BOARD THICKNESS:
SINGLE SIDED = 1.42 MIN.
DOUBLE SIDED = 2 MIN.
- 5 RECOMMENDED COMPONENT KEEP OUT AREA.
- 6 RECOMMENDED COMPONENT AND TRACES KEEP OUT AREA.
- 7 TE CONNECTIVITY LOGO MARKED IN APPROXIMATE AREA SHOWN.
- 8 PART NUMBER AND DATE CODE MARKED IN APPROXIMATE AREA SHOWN.





2292055-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SHIRK 06APR2015	TE Connectivity	
		CHK M. PHILLIPS 06APR2015		
DIMENSIONS:		APVD	NAME	
mm		PRODUCT SPEC	RECEPTACLE CONNECTOR, RIGHT ANGLE, 50 POSITION, SLIVER	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE	
0 PLC ±0.15		WEIGHT	A1	
1 PLC ±0.15		CUSTOMER DRAWING	C=2292055	
2 PLC ±0.15		SCALE	8:1	
3 PLC ±		SHEET	1 OF 2	
4 PLC ±		REV	A	
ANGLES				
FINISH				



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SHIRK 06APR2015		 TE Connectivity	
		CHW M. PHILLIPS 06APR2015			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE CONNECTOR, RIGHT ANGLE, 50 POSITION, SLIVER	
mm					
		PRODUCT SPEC			
		APPLICATION SPEC			
MATERIAL		WEIGHT		SIZE A1	
FINISH		CUSTOMER DRAWING		CAGE CODE -	
				DRAWING NO C-2292055	
				RESTRICTED TO -	
				SCALE 8:1	
				SHEET 2 OF 2	
				REV A	