


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



| REVISIONS | | | |
|-----------|-----------------|--------|-------------|
| REV | DESCRIPTION | DATE | CHANGED BY |
| A | INITIAL RELEASE | 2/4/08 | D.FRISIELLO |
| | | | |
| | | | |



NOTES:
 MATERIALS:
 HOOD: DIE-CAST ZINC ALLOY
 JACKSCREW: STEEL
 ASSEMBLY HARDWARE: STEEL
 STRAIN RELIEF GROMMETS: PVC, BLACK

FINISH:
 HOOD: NICKEL PLATED, MATTE FINISH ON MAJOR SURFACES
 JACKSCREW: NICKEL PLATED
 ASSEMBLY HARDWARE: NICKEL PLATED

MISCELLANEOUS:
 INTENDED FOR USE WITH 15 PIN STANDARD AND 26 PIN HIGH DENSITY D-SUBMINIATURE CONNECTORS.
 SUPPLIED WITH 5 STRAIN RELIEF GROMMETS FOR CABLING HAVING DIAMETERS RANGING FROM .190 TO .335 INCH.



FORMALLY MAC 95-110601

| | | |
|--|--|--------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] TOLERANCES TO BE: .X ±.1 [2.5] .XX ±.01 [.25] .XXX ±.005 [.13] OVERALL CABLE LENGTH TOL: ≤ 60 [1524] +3 [76.2] / -0 > 60 [1524] +5% / -0% | APPROVALS | DATE |
| | DRAWN BY D.FRISIELLO | 2/4/08 |
| | CHECKED BY R.FORTIN | 2/4/08 |
| | APPROVED BY S.SMITH | 2/4/08 |
| | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | |

| | | | |
|---|--------------------------|--|------------------|
| L-com CONNECTIVITY PRODUCTS | | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 | |
| CATEGORY DATA CABLING | | | |
| PRODUCT DESCRIPTION DB15 & HD26 HOOD KIT | | | |
| SIZE A | FSCM NO. 43321 | DWG. NO. SDC15AG | REV. A |
| SCALE: NONE CAD FILE: SDC15AG.SLDDRW | | | SHEET 1 OF 1 |