




**3-CONDUCTOR THROUGH TERMINAL
BLOCK CENTRE-/ LATERAL
MARKING for DIN 35 rail
2002-6301**



**3-CONDUCTOR THROUGH TERMINAL
BLOCK CENTRE-/ LATERAL
MARKING for DIN 35 rail
2002-6301**

ITEM-NO. (ITEM-NO.)	2002-6301
Cross section1 (Cross section / mm²)	0.25 - 2.5 (4)
Cross section2 (Cross section / AWG)	22 - 12
Strip length (Strip length / mm)	10 - 12
Measured voltage (Measured voltage / V)	800
Measured shock voltage (Measured shock voltage / kV)	8
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	24
Height (Height / mm)	39
Width (Width / mm)	5.2
Depth (Depth / mm)	52
No. of connection Points (No. of connection Points)	3
No. of potentials (No. of potentials)	1
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	5.718