



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	G in (mm)	H in (mm)	J in (mm)	K in (mm)	MAX. PANEL THICKNESS in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT 100 pcs lbs (g)
	MIN. in (mm)	MAX. in (mm)														
PLWP30SC	.12 (3)	1.18 (30)	.05 (1.3)	.19 (4.8)	.46 (11.7)	.22 (5.6)	.32 (8.1)	5.8 (147.3)	.74 (18.8)	.266 (6.8)	1.3 (33)	.30 (7.6)	.118 (3.0)	50 (222)	STANDARD	.32 (145)
PLWP40SC	.12 (3)	1.58 (40)	.05 (1.3)	.19 (4.8)	.46 (11.7)	.22 (5.6)	.32 (8.1)	7.0 (178)	.74 (18.8)	.266 (6.8)	1.3 (33)	.30 (7.6)	.118 (3.0)	50 (222)	STANDARD	.37 (168)
PLWP50SC	.12 (3)	1.97 (50)	.05 (1.3)	.19 (4.8)	.46 (11.7)	.22 (5.6)	.32 (8.1)	8.2 (208.3)	.74 (18.8)	.266 (6.8)	1.3 (33)	.30 (7.6)	.118 (3.0)	50 (222)	STANDARD	.42 (191)

NOTES:

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

CAD FILENAME/LAYERS										DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS						
										PANDUIT CORP. TINLEY PARK, ILLINOIS						
										WINGED PUSH MOUNT CABLE TIE PLWP30, 40, 50SC						
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±.1(2.5) (.XXX) ±.020(.51) (.XX) ±.02(.5) ANGLES ± ----				UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
										DRAWN BY SO	MAT'L:		SCALE NONE			
10	10/28/04	JABO		CHANGED FORMAT FOR CONSISTENCY SEE ECN FOR DETAILS			26267	10			DATE 12/14/90	HEAT STABILIZED NYLON 6.6 BLACK (-30)		DRAWING NO.	DWG SIZE	
REV	DATE	BY	CHK	DESCRIPTION			ECN - R	CUST	SUP		CHK'D HVP			SS-26267	A	