




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
S		REVISED PER ECO-16-004940	02AUG2016	NK	MZ
T		REVISED PER ECO-17-011181	05AUG2017	RS	MZ
U		REVISED PER ECO-18-000437	18JAN2018	RS	MZ



RECOMMENDED LAYOUT

- ① NYLON, UL 94-VO RATED, RED.
- ② PHOSPHOR BRONZE.
- ③ 3.81µm [.000150] MIN TIN-LEAD OVER 1.27µm [.000050] MIN NICKEL.
- ④ 0.76µm [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81µm [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- ⑤ 3.81µm [.000150] MIN TIN OVER 1.27µm [.000050] MIN NICKEL.
- ⑥ 0.76µm [.000030] MIN GOLD FOR A LENGTH OF 4.95 [.195] MIN FROM MATING END, 3.81µm [.000150] MIN TIN FOR A LENGTH OF 4.88 [.192] MIN ON OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- ⑦ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	⑥	NO	1-207524-0
	⑥	YES	207524-9
⑦ OBSOLETE	⑤	NO	207524-8
	⑤	YES	207524-7
OBSOLETE	④	NO	207524-4
OBSOLETE	④	YES	207524-3
OBSOLETE	③	NO	207524-2
OBSOLETE	③	YES	207524-1
		CONTACT FINISH	MOUNTING TABS
			PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	03/20/92		
		L.SIPE	3-25-92		
DIMENSIONS: mm [INCHES]		CHK	R.STONE	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	A.TRAVIS	SOCKET HEADER ASSEMBLY, 6 POSITION, METRIMATE	
0 PLC ± -		PRODUCT SPEC	108-10033	SIZE	CAGE CODE
1 PLC ± -		APPLICATION SPEC	-	A2	00779
2 PLC ± 0.25 [.010]		WEIGHT	-	DRAWING NO	RESTRICTED TO
3 PLC ± -		FINISH	-	C=207524	-
4 PLC ± -		CONTACT: SEE TABLE	-	SCALE	SHEET
ANGLES ± -				4:1	1 of 1
MATERIAL HOUSING: 1				REV	U
		CUSTOMER DRAWING			