

NOTE:
 1.MATERIAL:FPC PCB 79mm*10mm

THICKNESS:

PSA:3M 467

Pl:50um

BASE COPPER:18-20um

2.TOLERANCE ON ALL COPPER ARTWORK IS +/-0.05MM.

3.TOLERANCE ON ALL DIE CUTLINES IS +/-0.10MM.

4.TOLERANCE BETWEEN ARTWORK AND DIE CUTLINES IS +/-0.15MM.

5.Ni & Au PLATING ON SOLDER PADS ONLY

Ni:1-3um

Au:Min. 0.10um THICKNESS


6.COVER COAT:BLACK

PRINT TEXT

COLOR:WHITE;

TEXT HEIGHT:1.5MM

ISM 868/915 MHZ STAND ALONE ANTENNA



PART NUM	① FLEX	② CABLE	DIM. A
1052620001	1052621001	1052621004	93.6MM
1052620002	1052621001	1052621005	143.6MM
1052620003	1052621001	1052621006	193.6MM

ENTER DESCRIPTION EC NO:ABU2014-0055 DRWN:ZLRAO 2014/03/07 CHKDRANDY 2014/03/07 APPR:Chris Yu 2014/03/07	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE METRIC ONLY	SCALE 1:1	DESIGN UNITS MM	THIRD ANGLE PROJECTION	
			mm	INCH	DRAWN BY ZLRAO DATE 2014/03/07	ISM 868/915 MHZ STAND ALONE ANTENNA		
		4 PLACES	±	±	CHECKED BY RANDY DATE 2014/03/07			
		3 PLACES	±	±	APPROVED BY Chris Yu DATE 2014/03/07	molex DOCUMENT NO. SD-105262-001 SHEET NO. 1 OF 1		
2 PLACES	±	±	MATERIAL NO.					
1 PLACE	±	±	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE			
0 PLACE	±	±	ANGULAR ± °		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
REV C				SIZE A3				