
Thermofit Molded Parts Specification Control Drawing

Part Number : 322A112 thru 158 Description: Transition, 90° Side Breakout

NOTES

- 1. All dimensions are in $\frac{\text{Incres}}{\text{[millimeters]}}$
- 2. Dimensions appearing in table are as follows:
 - a As Supplied
 - b After Unrestricted Recovery
- Coating is optional. As supplied dimensions appearing in table are for uncoated ports. When coating is added, entry diameters will be reduced by .06 max.
- Molding ports are optional. When
 On modification number is
 specified molding ports will be
 located as shown. On size 322A112
 the vent port will be eliminated.






TABLE OF DIMENSIONS											
PART NUMBER	H & J		к		Р	R	S	Т	HW & JW	ĸw	
	Min	Max	Min	Max	±10%	±10%	±10%	±10%	±20%	±20%	
	a	b	a	ь	b	b	b	ь	b	ь	
322A112	.52 [13,2]	.23 [5,8]	.26 [6,6]	.12 [3,0]	2.06 [52,3]	1.03 [26,2]	.76 [19,3]	N/A	<u>.06</u> [1,52]	.04 [1,02]	
322A123	1.06 [26,9]	.49 [12,4]	.26 [6,6]	.12 [3,0]	3.28 [83,3]	1.64 [41,7]	1.07 [27,2]	<u>.42</u> [10,7]	<u>.10</u> [2,54]	<u>.04</u> [1,02]	
322A134	1.06 [26,9]	.50 [12,7]	.52 [13,2]	.23 [5,8]	4.24 [107,7]	2.12 [53,8]	1.52 [38,6]	. <u>80</u> [20,3]	<u>.10</u> [2,54]	<u>.06</u> [1,52]	
322A148	2.19 [55,6]	1.00 [25,4]	.52 [13,2]	.23 [5,8]	7.11 [180,6]	3.56 [90,4]	2.26 [57,4]	1 <u>.00</u> [25,4]	.18 [4,57]	.06 [1,52]	
322A158	2.19 [55,6]	1.00 [25,4]	1.06 [26,9]	<u>.49</u> [12,4]	8.75 [222,3]	4.38 [111,3]	3.06 [77,7]	1 <u>.50</u> [38,1]	<u>.18</u> [4,57]	.10 [2,54]	



TE CONNECTIVITY 300 CONSTITUTION DRIVE MENLO PARK, CALIFORNIA 94025

Revision: S1 Date: 20APR11

322A112 thru 158 Part Number :

Transition, 90° Description:

Side Breakout

Thermofit Molded Parts Specification Control Drawing


Part Number : 322A112 thru 158

Description :

Transition, 90° Side Breakout

COMPATABILITY CHART									
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION				
-3	Polyolefin, Semi-rigid	RT-301	/42; /86	S-1017; S-1048	Adhesive				
-4	Polyolefin, Flexible	RT-1304	/42; /86	S-1017; S-1048	Adhesive				
-5	Elastomer, Flexible	RT-501	/42	S-1017	Adhesive				
-6	Silicone	RT-602	N/A						
-12	*VITON, Flexible	RT-1312	N/A						
-25	Elastomer, Fluid Resistant	RT-1325	/42; /86	S-1017; S-1048	Adhesive				
-100	Polyolefin, Semi-flexible ZEROHAL	RT-1323	/86; /180	S-1048; S-1030	Adhesive				

*VITON is a Registered Trademark of Dupont



IF THIS DOCUMENT IS PRINTED IT BECOMES UNCONTROLLED. CHECK FOR THE LATEST REVISION.

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION



TE CONNECTIVITY
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision: S1 Date: 20APR11 Part Number : Description :

322A112 thru 158

Transition, 90° Side Breakout

CAD FILE MP00071