





NO.	MASSE / DIMENSIONI
A	43
B	49.5
C	36.6
D1	1 1/2-18UNEF-2A
D2	34.93
D3	19.1
D4	55
E	2.03
K	5.46
L1	50.2
L2	22.5
L3	4

NO.	BESCHREIBUNG / DESCRIPTION
1	ISOLIERKÖRPER BUCHSE / INSULATOR SOCKET
2	ISOLIERKÖRPER MITTE / WAVER
3	DICHTRING / GASKET
4	DICHTKÖRPER / GROMMET
5	ENDRING / ENDRING
7	KONTAKT BUCHSE / CONTACT SOCKET
8	GEHÄUSE / RECEPTACLE
9	ENDGEHÄUSE / ENDBELL
10	O-RING / O-RING
11	SECHSKANTMUTTER / HEX NUT
15	KABELTÜLLE / BUSHING
16	KABELKLEMME / CABLE CLAMP
19	BAYONETTSTIFT / BAYONET PIN
20	ZYLINDER-SCHRAUBE / CYLINDER HEAD SCREW



Note: Due to an automatic nomenclature system, numbers generated may not be sequential.

Specification and Dimensions subject to change
Drawings illustrate normal insulator positioning

Material Specification:

Shell Material:	Aluminium alloy
-----------------	-----------------

Shell Plating:	Olive drab chromate over cadmium plating
----------------	--

Insulator Material: Polychloroprene

Contact Material:	Copper alloy
-------------------	--------------

Contact Plating:	#12/16:gold plated, #20:contact area gold plated
------------------	--

all dimensions are in mm
Dimensions without tolerance indications are general tolerances in acc. with DIN7168m

drawing for
CUSTOMER

Engineered for life

ITT CANNON GmbH
D - 71384 Weinstadt/Germany

description	KPSE07F22-55S
-------------	---------------

Jam nut receptacle

Grommet seal with strain relief

Crimp Contacts / Socket / Layout: 22-55

© All rights reserved. Reproduction or issue to third in any form whatever is only permitted with written authorization of ITT Cannon



page	revision
1/1	1572 20. Dec 17