





▲ SWITCH FUNCTION




POS. 1	POS. 2
1-2	(3-4)

() = MOMENTARY





NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NOS. FOR REF. ONLY
- ▲ 4. FUNCTION: DPDT
- ▲ 5. RATING: 2A @ 48VDC
6. ILLUMINATION VOLTAGE: BASE VOLTAGE 2.8 V
7. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
8. INSULATION RESISTANCE: 1,000M Ω @ 500VDC
9. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
10. ELECTRICAL LIFE: 50,000 CYCLES
11. OPERATING TEMPERATURE: -20°C TO 55°C
12. INGRESS PROTECTION: IP65
13. SUPPLIED HARDWARE: O-RING AND HEXNUT
14. ▲ DENOTES CRITICAL PARAMETER
15. 2011/65/EU (ROHS) COMPLIANT



DOT DENOTES
LED COLOR



E-SWITCH®

B	22589	Update to correct Housing	11/10/16	MW
A	21519	New Release	7/16/14	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV9F2V0SS-331

SCALE 1:1

DATE 7/16/2014

DR rc

DWG 52-PV9F2V0SS331

REV B