









▲

SWITCH FUNCTION	
POS. 1	POS. 2
1-2	(3-4)

() = MOMENTARY



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NOS. FOR REF. ONLY
- FUNCTION: DPDT
- RATING: 2A @ 48VDC
- ILLUMINATION VOLTAGE: BASE VOLTAGE 2.8 V
- CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
- INSULATION RESISTANCE: 1,000MΩ @ 500VDC
- DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
- ELECTRICAL LIFE: 50,000 CYCLES
- OPERATING TEMPERATURE: -20°C TO 55°C
- INGRESS PROTECTION: IP65
- SUPPLIED HARDWARE: O-RING AND HEXNUT
- ▲ DENOTES CRITICAL PARAMETER
- 2002/95/EC (ROHS) COMPLIANT
- ILLUMINATION COLOR: BLUE (FORWARD), BLUE (REVERSE)



B	21957	UPDATE TO CORRECT HOUSING	10/15/15	MW
A	21519	New Release	7/16/14	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV9F2V0SS-341

SCALE 1:1

DATE 7/16/2014

DR rc

DWG 52-PV9F2V0SS341

REV B