





This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.

Customer drawing







Dimensions

Positions	A	B	C	E	F
15	30.81	24.99	16.92	2.29	19.20
26	39.20	33.30	25.25	2.29	27.70
44	53.04	47.04	38.96	2.29	41.10
62	69.40	63.50	55.42	2.41	57.30



78 Positions



REVISIONS

SYM	ECN	DESCRIPTION	DATE	APPROVED
2	HK--	Add the dimension	08/14/09	IP
3	HK--	Add the wire size	09/26/11'	IP
4	HK--	Updated the wire size	10/13/11'	IP
5	HK--	Change dim. 30.84 to 30.81mm	08/27/13	IP
6	HK--	Add pin number	08/31/17	IP

D-SUB TECHNICAL DATA

SHELL : Steel, 100u" min Tin over 50u" min nickel over 50u" min Copper
BODY : Glass-Filled Thermoplastic PBT, UL94V-0, color black
CONTACTS : Copper alloy
Gold flash over 50u" min nickel on mating area
100u" min tin over 50u" min nickel on solder area
ELECTRICAL : Voltage rating 250 VAC/RMS
Current Rating :3 AMP
Withstanding Voltage >1000 VAC/RMS
Insulation resistance >1000 M Ohms
Contact resistance 20 mOhms max
MARKING : Amphenol---...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

L 717 HD X XX P

L:RoHS Compliance

717: tinned shell +
dimples for plug

HD: High density

Contact type:
P: Pin

Configuration:
15, 26, 44, 62, 78

Shell Size :E,A,B,C,D

UNLESS OTHERWISE SPECIFIED TOLERANCES	
U.S.	METRIC
.X +/-	0.50
.XX +/-	0.30
.XXX +/-	0.20
FRACTIONS +/-	5°
ANGLES +/-	
FOR MATERIALS AND FINISHES SEE NOTES	
REMOVE SHARP EDGES	
DIMENSIONS	
U.S.	INCHES
METRIC	MM

APPROVAL		DATE
DRAWN	Simon Chen	08/31/17
CHECKED	Tony Tang	08/31/17
DRAWING FILE :		
ANGLE OF PROJECTION		

Amphenol		
TITLE D-Sub connector,HD Solder type		
SIZE	DRAWING NO.	REV.
A4	L717HDXXXP	6
SCALE	NONE	SHEET 1 OF 1