

F

E

D

C

B

A

F

E

D

C

B

A

REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
02	△△	變更塑膠用料	22.04.2008	周禮軍
03	△△	新增膠紙配方	2008.10.20	許承佑
04	△△	Change Part NO.	2009.02.27	李小珍
05	△△	增加溝槽及變更新圖號	2011.08.05	郭丙建

Specifications

Current Rating: 1.0Amp

Insulation Resistance: 1000MΩ Min.

Dielectric Withstanding: 300V AC

Contact Resistance: 20mΩ Max.

Operating Temperature: -40°C to +105°C





Materials

Contact Material: Phosphor Bronze

Insulator Material: Polyester UL94V-0

△ LCP

All materials must meet Greenconn requirement for environment protection.



△ Ordering Information

C	SEC208	-	XX		XX	A	001	C	1		A	X
No. of Pins per Row		Standard Plating		Color		Standard Packing						
02~40		02=Gold Flash		1=Black		A=box						
		Selective Plating				Selective Packing						
		01= Tin				C=Tube						
		05=Gold Flash/Tin										

格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE

X.*±5.0°	X.±0.30
.X*±3.0°	.X±0.25
.XX*±2.0°	.XX±0.15
.XXX*±1.0°	.XXX±0.10

DESIGN: 郭丙建

DATE: 2011.08.05

CHECKED: 管葉波

DATE: 2011.08.05

AUDITED: 陳義昌

DATE: 2011.08.05

DWG. NO.

C SEC208-CA1CA

PART NO.

C SEC208-XXXX A001C1AX

TITLE.

1.27 FEMALE HEADER
DUAL ROWS SMT TYPE
BASE 3.45H

REV.	UNIT.	SCALE.	PAGE.
05	mm	5:1	1/1