




Front view and mounting




Side view



Rear view





Y view




| SPECIFICATION | CONNECTION | BIPOLAR PARALLEL |
|-----------------------------|------------|------------------------|
| SUPPLY VOLTAGE (VDC) | | 12 TO 48 Δ |
| AMPS/PHASE | Δ | * UP TO 4.8 (100%=3.2) |
| HOLDING TORQUE (Nm) [lb-in] | | 1.98 [17.52] |
| DETENT TORQUE (Nm) [lb-in] | | 0.068 [0.602] |
| STEP ANGLE (°) ± ACCURACY | | * 1.8 TO MICROSTEP |
| WEIGHT (Kg) [lb] | | 1.22 [6.54] |

* ADJUSTABLE WITH NANOPRO.



PERMISSIBLE RADIAL+AXIAL FORCE



| AXIAL-FORCE F_a (N) | $F_a=10$ | | | |
|------------------------|----------|-------|--------|----|
| DISTANCE a (mm) | 5 | 10 | 15 | 20 |
| RADIAL-FORCE F_r (N) | 130 | 90 | 70 | 52 |
| | | AXIAL | RADIAL | |
| SHAFT PLAY (mm) | 0.08 | 0.02 | | |
| AT LOAD MAX: (N) | 4.5 | 4.5 | | |

| JST PHDR-8VS | | |
|--------------|-------------|------------|
| PIN No. | WIRE COLOUR | ASSIGNMENT |
| 1 | BU | GND |
| 2 | WH-PK | +UB extern |
| 3 | YE | RS485 Rx- |
| 4 | GN | RS485 Rx+ |
| 5 | PK | RS485 Tx- |
| 6 | GY | RS485 Tx+ |
| 7 | BN | CAN+ |
| 8 | WH | CAN- |

| JST PHDR-12VS | | |
|---------------|----------------|--------------|
| PIN No. | WIRE COLOUR | ASSIGNMENT |
| 1 | GY-BN | COM |
| 2 | RD | GND |
| 3 | BK | INPUT 1 |
| 4 | VT | INPUT 2 |
| 5 | GY-PK Δ | INPUT 3 |
| 6 | RD-BU | INPUT 4 |
| 7 | WH-GN Δ | INOUT 5 |
| 8 | BN-GN | INPUT 6 |
| 9 | WH-BU | ANALOG INPUT |
| 10 | WH-YE | OUTPUT 1 |
| 11 | YE-BN | OUTPUT 2 |
| 12 | WH-GY | OUTPUT 3 |

| FK-MCP-1.5/2-ST-3.5 gn | | |
|------------------------|-------------|------------|
| PIN No. | WIRE COLOUR | ASSIGNMENT |
| 1 | BK | GND |
| 2 | BN | Vcc |

| FULL STEP 2 PHASE-Ex., WHEN FACING MOUNTING END (X) | | | | | |
|---|---|---|----|----|---------------------|
| STEP | A | B | A\ | B\ | |
| 1 | + | + | - | - | CCW ↑ ↓ CW |
| 2 | - | + | - | - | |
| 3 | - | - | + | + | |
| 4 | + | - | - | + | |

CABLE SET:
ZK-PD4N
L=500mm

| | | | |
|---|--|--|--|
| OVERTEMPERATURE PROTECTION (ELECTRONICS): 80°C | | | |
| AMBIENT TEMPERATURE -10°~ 40°C [14°F ~ 104°F] (HIGHER TEMPERATURE REDUCES DUTY CYCLE) | | | |
| INSULATION RESISTANCE 100 MOhm (UNDER NORMAL TEMPERATURE AND HUMIDITY) | | | |
| INSULATION CLASS B 130° [266°F] | | | |
| DIELECTRIC STRENGTH 500VAC FOR 1 MIN. (BETWEEN THE MOTOR COILS AND THE MOTOR CASE) | | | |
| AMBIENT HUMIDITY MAX. 85% (NO CONDENSATION) | | | |

| | | | |
|-----|-------------------------------|-----------|------|
| 3 | MOTOR LENGTH | 20.07.10. | J.W. |
| 5 | NEW VALUE OF SUPPLY VOLTAGE | 15.12.10. | J.W. |
| 4 | NEW CONNECTION OF IN-, OUTPUT | 07.09.10. | J.W. |
| REV | DESCRIPTION | DATE | APVD |



PD4-N5918L4204

| | | | |
|------------|-----------|-------|----------|
| SCALE FREE | APVD | S.Ha. | 30.10.09 |
| X ±0.5 | CHKD | | |
| 1PL ±0.2 | DRN | J.W. | 30.10.09 |
| 2PL ±0.1 | SIGNATURE | | |
| ANGLE ±30' | | | |

PLUG&DRIVE MOTOR

DWG.NO
PD4-N5918L4204