




COIL: 26.5 VDC

WINDING #1

1000 OHMS ± 10% @ 25° C

13.0 VDC MUST OPERATE

26.5 VDC NOMINAL VOLTAGE

WINDING #2

1000 OHMS ± 10% @ 25° C

13.0 VDC MUST OPERATE

26.5 VDC NOMINAL VOLTAGE

ENVIRONMENT:

VIBRATION 10 CPS TO 2500 CPS @ 30 g's

SHOCK 100 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C


NOTES: OTHER SPECIFICATIONS IN ACCORDANCE WITH MIL-R-39016/45

OPERATE TIME 5 MS MAX

STABILIZATION TIME 2.5 MS MAX

CUSTOMER DATA SHEET

LAST ENERG.



CONTACT RATING: LOW LEVEL TO 2 AMPS
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 10/1/96

CK. *[Signature]* 10/1/96



COMMUNICATIONS
INSTRUMENTS, INC.

CUST. COMMERCIAL
CUST. NO. REF. M39016/45-021M

TYPE "LS" RELAY

LS-9521M