





RELATED DOCUMENTS

SEE SPECIFICATIONS

CABLE LENGTH	TOLERANCE *		
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER		
STRIP LENGTH	TOLERANCE *		
0-7mm	±0.5mm		
8-29mm	±1.0mm		
30-49mm	±2.0mm		
50-69mm	±3.0mm		
70-100mm	±4.0mm		
OVER 100mm	±5.0mm		
* UNLESS OTHERWISE SPECIFIED			

SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:

- 1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
- 2. "/S90" INDICATES POLYURETHANE (TPU) CABLE JACKET.
- 3. "/S101" INDICATES FLEXLIFE-20 AND CTRACK CABLE.

J	UPDATE SOURCE DRAWING - ADD CTRACK TO /S101 NOTE	СВМ	02/18/14	44634
REV	DESCRIPTION	BY	DATE	ECO NO.

•				
b.	l (♥) €-+			
·•				
MATERIAL				
SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY			
INISH				
SEE SPECIFICATIONS	CONTACT TURCK FOR MORE INFORMATION			

3RD ANGLE

PROJECTION

Turck inc High Technology Sensors and Automation Controls

FILE: 777006586

3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com

SHEET 1 OF 1

DATE 07/07/06 MJM PKG 3M-*/S90/S101 SCALE 1=1.0 UNIT OF MEASUREMENT

MILLIMETER [INCH]

DO NOT SCALE THIS DRAWING

THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS

DOCUMENT WITHOUT
WRITTEN PERMISSION IS
PROHIBITED.

IDENTIFICATION NO. REV