

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

REVISIONS






P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECO-17-016472	20NOV2017	AP	DG

NOTES:
RATED CURRENT:3.0AMP
CONTACT RESISTANCE:30MΩ MAX
WITHSTAND VOLTAGE:500V AC
INSULATION RESISTANCE:1000MΩ MIN
OPERATION TEMPERATURE:-55℃ TO +105℃

INSULATOR:PA9T+G.F UL94V-0 BLACK
CONTACT:PHOSPHOR BRONZE
" GOLD PLATING ON CONTACT AREA
100u" MATTE TIN PLATING ON SOLDER TAIL
50u" NICKEL UNDERPLATED OVERALL
HOLD DOWN:BRASS,100u" TIN OVER 50u" NICKEL
SHEEL:SPCC,50u" NICKEL PLATING OVERALL
SCREWLOCK:BRASS,30u" NICKEL PLATING OVERALL

LOT NUMBER "XXXX"
STANDS FOR CALENDAR YEAR
STANDS FOR WEEK NUMBER

RECOMMENDED P.C.B LAYOUT(TOP SIDE)
(PCB BOARD TOLERANCE±0.05)



4.10 [0.161]	THREADED SEE DETAIL Z	30μ" Au	2311763-3
4.10 [0.161]	THREADED SEE DETAIL Z	Au Flash	2311763-2
3.80 [0.150]	YES	30μ" Au	2311763-1
X ± 0.30 [± 0.012]	SCREWLOCK	Contact Area	P/N
BOARDLOCK LENGTH		Plating	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI 03MAR2017	 TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK GORENC, DANIEL L 03MAR2017		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD GORENC, DANIEL L 03MAR2017	NAME AMPLIMITE RECEPTACLE, HD22, RIGHT ANGLE, 15P	
0 PLC ± - 1 PLC ± 0.40 2 PLC ± 0.25 3 PLC ± 0.15 4 PLC ± - ANGLES ± 3°		PRODUCT SPEC	-	
MATERIAL		FINISH	-	
-		-	-	
CUSTOMER DRAWING		WEIGHT	-	
			SIZE A2	RESTRICTED TO -
			CAGE CODE 00779	REV C
			DRAWING NO. C-2311763	
			SCALE 1:1	
			SHEET 1 OF 1	