







FEMALE END VIEW	TYPICAL PANEL CUTOUT	TYPICAL BOARD LAYOUT	SPECIFICATIONS	
 		 SCALE: 2=1	CONTACT CARRIER MATERIAL/COLOR	NYLON OR TPU/BLACK
			CONTACT MATERIAL/PLATING	BRASS/GOLD
			HOUSING/LOCKNUT MATERIAL/PLATING	BRASS/NICKEL
			RATED CURRENT [A]	1.5 A
			RATED VOLTAGE [V]	60 VAC/75 VDC
			NUMBER OF CONDUCTORS [AWG]	PRINTED CIRCUIT PINS
			TEMPERATURE RATING	-40°C TO +90°C (-40°F TO +194°F)
			PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68
			MAX. PANEL THICKNESS	3.0 [0.12]



SOURCE DRAWING - FOR REFERENCE ONLY

<div>RELATED DOCUMENTS</div> <div>1.</div> <div>2.</div> <div>3.</div> <div>4.</div>					<div>3RD ANGLE PROJECTION</div> <div></div>		<div>THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</div> <div><div><div>3000 CAMPUS DRIVE</div><div>MINNEAPOLIS, MN 55441</div><div>1-800-544-7769</div><div>(763) 553-7300</div><div>(763) 553-0708 fax</div><div>turck.com</div></div><div><div><div>TURCK INC</div><div>High Technology Sensors and Automation Controls</div></div></div></div>		
					<div>DRFT CBM</div> <div>DATE 06/20/00</div> <div>APVD</div> <div>SCALE 1 = 1.0</div> <div>UNIT OF MEASUREMENT</div> <div>MILLIMETER [INCH]</div> <div>DO NOT SCALE THIS DRAWING</div>		<div>DESCRIPTION</div> <div>FKFD 8</div> <div>IDENTIFICATION NO.</div> <div>U4501-3</div> <div>REV</div> <div>E</div>		
					<div>MATERIAL</div> <div>SEE SPECIFICATIONS</div>		<div>ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY</div> <div>CONTACT TURCK FOR MORE INFORMATION</div>		
<div>FINISH</div> <div>SEE SPECIFICATIONS</div>									
E	ADD END VIEW OR UPDATE END VIEW TO SHOW APPROPRIATE ORIENTATION OF FLATS AND KEYWAY	TV	02/03/16	53385					
REV	DESCRIPTION	BY	DATE	ECO NO.					