


	10	9	8	7		6	5	4	3	2	19324				
	MATERIAL NUMBER	ALTERNATE PART NUMBER	NOM WIRE SIZE AND RANGE (MM ²)	NOM BOLT SIZE (MM)	INSULATION COLOR (REF)	DIMENSIONS									
						d1 MIN	a2 ±1.0	d1 MIN	d2 ±0,7	d3 ±0,25	d4+0,5/-0	L MAX	r MIN	s1 NOM	s2 MIN
F	193240001	AA1-832-M2,5	1 (0,5 - 1)	2,5	RED	4,25	10,0	1,6	2,77	6,45	3,2	17,3	4	0,71	0,4
	193240002	AA1-832-M3	1 (0,5 - 1)	3		4,25	10,0	1,6	3,29	6,45	3,2	17,3	4,5	0,71	0,4
	193240003	AA1-832-M3,5	1 (0,5 - 1)	3,5		4,25	10,0	1,6	3,79	6,45	3,2	17,3	4,5	0,71	0,4
	193240004	AA1-821-M4	1 (0,5 - 1)	4		4,25	10,0	1,6	4,39	7,92	3,2	18,1	6	0,71	0,4
	193240005	AA1-822-M5	1 (0,5 - 1)	5		4,25	10,0	1,6	5,39	11,86	3,2	21,0	6,5	0,71	0,4
	193240006	BB2,5-823-M3	2,5 (1 - 2,5)	3	BLUE	4,25	10,5	2,1	3,29	6,35	4,1	16,8	4,5	0,79	0,4
	193240007	BB2,5-823-M3,5	2,5 (1 - 2,5)	3,5		4,25	10,5	2,1	3,79	6,35	4,1	16,8	4,5	0,79	0,4
	193240008	BB2,5-837-M4	2,5 (1 - 2,5)	4		4,25	10,5	2,1	4,39	7,92	4,1	18,5	6	0,79	0,4
E	193240009	BB2,5-839-M5	2,5 (1 - 2,5)	5		4,25	10,5	2,1	5,39	8,69	4,1	19,2	6,5	0,79	0,4
	193240010	BB2,5-825-M6	2,5 (1 - 2,5)	6		4,25	10,5	2,1	6,61	11,86	4,1	21,3	7,5	0,79	0,4
	193240011	BB2,5-818-M8	2,5 (1 - 2,5)	8	YELLOW	4,25	10,5	2,1	8,51	13,56	4,1	25,1	10	0,79	0,4
	193240012	C6-836-M4	6 (2,5 - 6)	4		6,00	14,0	3,3	4,39	7,16	5,6	23,1	6	1,02	0,5
	193240013	C6-828-M5	6 (2,5 - 6)	5		6,00	14,0	3,3	5,39	9,53	5,6	23,0	6,5	1,02	0,5
	193240014	C6-830-M6	6 (2,5 - 6)	6		6,00	14,0	3,3	6,61	13,46	5,6	25,3	7,5	1,02	0,5
	193240015	C6-830-M8	6 (2,5 - 6)	8		D	6,00	14,0	3,3	8,51	13,46	5,6	25,3	10	1,02
	193240016	C6-840-M10	6 (2,5 - 6)	10	6,00		14,0	3,3	10,63	14,94	5,6	27,1	12	1,02	0,5




NOTES:

- MATERIALS:
TERMINAL: TIN-PLATED COPPER.
STRAIN-RELIEF FERRULE: TIN-PLATED COPPER ALLOY
INSULATION: NYLON (SEE CHART FOR COLOR)
- PARTS ARE ROHS COMPLIANT.

SALES DRAWING

ADD COLOR REF EC NO: IPG2017-0610 2017/01/04 DRAWN: JAS01 CHKD: JMACNEIL APPR: JMACNEIL 2017/01/25		QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 	
				mm		INCH		DRAWN BY ETHRODAHL		DATE 2012/07/17	
				4 PLACES ± ---		± ---		CHECKED BY JMACNEIL		DATE 2012/07/17	
				3 PLACES ± ---		± ---		APPROVED BY JMACNEIL		DATE 2012/12/11	
				2 PLACES ± 0.05		± ---		 MOLEX INCORPORATED		SHEET NO. 1 OF 1	
				1 PLACE ± 0.10		± ---					
				ANGULAR ± ---°				DOCUMENT NO. SD-19324-001			
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART					
						SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

	10	9	8	7		6	5	4	3	2	19324				
	MATERIAL NUMBER	ALTERNATE PART NUMBER	NOM WIRE SIZE AND RANGE (MM ²)	NOM BOLT SIZE (MM)	INSULATION COLOR (REF)	DIMENSIONS									
						d1 MIN	a2 ±1.0	d1 MIN	d2 ±0,7	d3 ±0,25	d4+0,5/-0	L MAX	r MIN	s1 NOM	s2 MIN
F	193240001	AA1-832-M2,5	1 (0,5 - 1)	2,5	RED	4,25	10,0	1,6	2,77	6,45	3,2	17,3	4	0,71	0,4
	193240002	AA1-832-M3	1 (0,5 - 1)	3		4,25	10,0	1,6	3,29	6,45	3,2	17,3	4,5	0,71	0,4
	193240003	AA1-832-M3,5	1 (0,5 - 1)	3,5		4,25	10,0	1,6	3,79	6,45	3,2	17,3	4,5	0,71	0,4
	193240004	AA1-821-M4	1 (0,5 - 1)	4		4,25	10,0	1,6	4,39	7,92	3,2	18,1	6	0,71	0,4
	193240005	AA1-822-M5	1 (0,5 - 1)	5		4,25	10,0	1,6	5,39	11,86	3,2	21,0	6,5	0,71	0,4
	193240006	BB2,5-823-M3	2,5 (1 - 2,5)	3	BLUE	4,25	10,5	2,1	3,29	6,35	4,1	16,8	4,5	0,79	0,4
	193240007	BB2,5-823-M3,5	2,5 (1 - 2,5)	3,5		4,25	10,5	2,1	3,79	6,35	4,1	16,8	4,5	0,79	0,4
	193240008	BB2,5-837-M4	2,5 (1 - 2,5)	4		4,25	10,5	2,1	4,39	7,92	4,1	18,5	6	0,79	0,4
E	193240009	BB2,5-839-M5	2,5 (1 - 2,5)	5		4,25	10,5	2,1	5,39	8,69	4,1	19,2	6,5	0,79	0,4
	193240010	BB2,5-825-M6	2,5 (1 - 2,5)	6		4,25	10,5	2,1	6,61	11,86	4,1	21,3	7,5	0,79	0,4
	193240011	BB2,5-818-M8	2,5 (1 - 2,5)	8	YELLOW	4,25	10,5	2,1	8,51	13,56	4,1	25,1	10	0,79	0,4
	193240012	C6-836-M4	6 (2,5 - 6)	4		6,00	14,0	3,3	4,39	7,16	5,6	23,1	6	1,02	0,5
	193240013	C6-828-M5	6 (2,5 - 6)	5		6,00	14,0	3,3	5,39	9,53	5,6	23,0	6,5	1,02	0,5
	193240014	C6-830-M6	6 (2,5 - 6)	6		6,00	14,0	3,3	6,61	13,46	5,6	25,3	7,5	1,02	0,5
	193240015	C6-830-M8	6 (2,5 - 6)	8		D	6,00	14,0	3,3	8,51	13,46	5,6	25,3	10	1,02
	193240016	C6-840-M10	6 (2,5 - 6)	10	6,00		14,0	3,3	10,63	14,94	5,6	27,1	12	1,02	0,5



NOTES:

- MATERIALS:
TERMINAL: TIN-PLATED COPPER.
STRAIN-RELIEF FERRULE: TIN-PLATED COPPER ALLOY
INSULATION: NYLON (SEE CHART FOR COLOR)
- PARTS ARE ROHS COMPLIANT.

SALES DRAWING

ADD COLOR REF EC NO: IPG2017-0610 2017/01/04 DRAWN: JAS01 CHKD: JMACNEIL APPR: JMACNEIL 2017/01/25		QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
2	REV			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	4 PLACES	± ---	± ---	DRAWN BY ETHRODAHL	DATE 2012/07/17	TITLE METRIC RING TERMINALS AVIKRIMP 0,5 - 6 MM2
					3 PLACES	± ---	± ---	CHECKED BY	DATE	
					2 PLACES	± 0.05	± ---	JMACNEIL	2012/07/17	MOLEX INCORPORATED
					1 PLACE	± 0.10	± ---	APPROVED BY	DATE	
					ANGULAR ± ---°		JMACNEIL	2012/12/11	DOCUMENT NO. SD-19324-001	
							MATERIAL NO.			
		SEE CHART								
		SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						