

DESCRIPTION: 97 SERIES SOLDER STYLE PANEL & CABLE MOUNT

D-SUB CONNECTORS

MODEL NUMBER: 40-97XXS

APPLICATION: FOR CABLE

CRIMP TOOL: N/A

IMPEDANCE: N/A

FEQUENCY RANGE: 0-15 MHz


MATERIAL: HOUSING STEEL NICKEL PLATED

INSULATOR PBT+FIBER-GLASS UL94-V0 WHITE


CONTACT COPPER-ALLOY, GOLD PLATED

RoHS COMPLIANCE: YES

TECHNICAL DETAIL: N/A



MODEL NUMBER	PIN	А	В	С	D
40-9709S	09	30.80	24.99	16.30	19.20
40-9715S	15	39.15	33.32	24.65	27.70
40-9725S	25	53.00	47.04	38.40	41.10
40-9737S	37	69.30	63.50	54.80	57.30



DIM OUTLINE

сопск соместиту зацитомя о веј доцр	3RD ANGLE PROJECTION	AIM-Cambridge			
	RoHS 2002/95/EC	Title: D-Sub Connector, 97 Series, Solder Style Panel and Cable Mount, Female			
This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and	UNLESS OTHERWISE SPECIFIED UNITS: METRIC	Model No.			
issued with the clear understanding that it is not traced or copied without permission and is returnable upon demand. INTERPRET DRAWING IN ACCORDANCE WITH ASME	.XX ±.51	40-97XXS			
	.XXX ±.127 ANGLES ±2°	Size DO NOT SCALE Date: 9/9/2013 Sheet 1 of 1			