THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

RoHS 2002/95/EC

FLECTRICAL CHARACTERISTICS @ 25°C

ELECTRICAL SPECIFICATIONS:

1.0 TURNS RATIO: (P6-P5-P4): (J6-J3) : 1CT : 1CT ± 3% (P3-P2-P1): (J2-J1) : 1CT : 1CT ± 3%

2.0 INDUCTANCE: (P6-P4) : 350uH MIN. @ 0.1V, 100KHz, 8mA DC Bias (P3-P1) : 350uH MIN. @ 0.1V, 100KHz, 8mA DC Bias

3.0 LEAKAGE INDUCTANCE: P6-P4 (WITH J6 AND J3 SHORT) : 0.3 MAX. @ 1MHz P3-P1 (WITH J2 AND J1 SHORT) : 0.3 MAX. @ 1MHz

4.0 INTERWINDING CAPACITANCE: (P6,P5,P4) TO (J6,J3) : 30pf MAX @ 1MHz (P3,P2,P1) TO (J2,J1) : 30pf MAX. @ 1MHZ

5.0 DC RESISTANCE: (J6-J3)=(J2-J1) : 1.2 ohms Max.

<u>RECEIVE</u>

6.0 RETURN LOSS: 1MHz TO 30MHz : 18dB MIN.

60MHz TO 80MHz : 12dB MIN.

NOTE: 100 OHMS CONNECTED TO (J2-J1) OR (J6-J3).

7.0 DIELECTRIC WITHSTAND: (J1, J2) TO (P1, P3) : 1500 Vrms (J3, J6) TO (P4,P6) : 1500 Vrms

8.0 INSERTION LOSS: RS=RL=100 ohms

100KHz TO 100MHz : 1.1 dB TYP

9.0 RISE TIME: RS=100 OHMS AND RL = 100 OHMS


OUTPUT VOLTAGE = 1 V peak : 3.0 nS MAX PULSE WIDTH= 112nS : 3.0 nS MAX

10.0 CROSS TALK: 1MHz TO 100MHz : 40 dB TYP

TITLE

11.0 COMMON TO COMMON MODE ATTENUATION:

30MHz TO 100MHz : 35dB TYP



NOTES

1.0 PINS WITHOUT ELECTRICAL CONNECTION ARE OMITTED.

ORIGINATED BY	DATE
Bain Liu	09-04-08
DRAWN BY	DATE
LW Yuan	09-04-08


10/100BT
TAB DOWN, SHIELDED
PATENTED

PART NO. / DRAWING NO.	STANDARD DIM. TOL. IN INCH		[] METRIC DIM. AS REFERENCE		
SI-60062-F			UNIT : INCH [mm]	REV.: B0	
FILE NAME	X		SCALE: N/A	SIZE: A4	
SI-60062-F.DWG	XXX	±0.005		PAGE: 2	




THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.







LED POLARITY (ENLARGED VIEW)







LED SPECIFICATION					
STANDARD LED	WAVELENGTH	Forward V (MAX)	*(TYP)		
GREEN	565 nm	2.5 V	2.2 V		
YELLOW	590 nm	2.5 V	2.1 V		



NOTES:


- 1. CONNECTOR MATERIALS:
 HOUSING: THERMOPLASTIC UL94 V-0
 CONTACT/SHIELD: COPPER ALLOY
 SHIELD PLATING: NICKEL OR TIN
 CONTACT PLATING: SELECTIVE GOLD,
 50 MICRO-INCHES MIN. IN CONTACT AREA.
- 2. PIN NOT ELECTRICALLY CONNECTED MAYBE OMITTED. SEE ELECTRICAL DRAWING FOR OMITTED PINS.
- 3. TOLERANCES COMPLY WITH F.C.C. DIMENSION REQUIREMENTS.
- 4. ALL TOLERANCES NOT OTHERWISE SPECIFIED TO BE ±.005 [0.13]
- 5. WAVE SOLDER COMPATIBLE PREHEAT 125°C/90SECS.


ORIGINATED BY	DATE	Maglack	PART NO. / DRAWING NO.	STANDA	RD DIM.	[] METRIC DIM. AS REI	ERENCE
Bain Liu	09-04-08	. •	SI-60062-F	TOL. IN	INCH	UNIT : INCH [mm]	REV.: B0
DRAWN BY	DATE	10/100BT	FILE NAME	X xx		SCALE: N/A	SIZE: A4
LW Yuan	09-04-08	TAB DOWN, SHIELDED PATENTED	SI-60062-F.DWG	XXX	±0.005		PAGE: 3



THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.







- THE SUGGESTED PANEL OPENING IS INTENDED
 TO GIVE THE USER THE ABILITY TO HAVE
 REASONABLE JACK / PANEL CLEARANCES
 YET MAINTAIN RELIABLE GROUNDING
 CAPABILITY.
- 2. ALL TOLERANCES NOT OTHERWISE SPECIFIED TO BE ±.005 [0.13]

ORIGINATED BY	DATE
Bain Liu	09-04-08
DRAWN BY	DATE
LW Yuan	09-04-08

10/100BT
TAB DOWN, SHIELDED
PATENTED

TITLE

PART NO. / DRAWING NO.	TOL IN INCH		[] METRIC DIM. AS REFERENCE			
SI-60062-F			UNIT : INCH [mm]	REV.: B0		
FILE NAME	X	_/	SCALE: N/A	SIZE: A4		
SI-60062-F.DWG	XXX	±0.005	—	PAGE: 4		

