


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F3	ECR-17-012638	11JAN2018	RK	PS


CLAMPING SCREW TEST FACILITY



INTERLOCKING FEATURE

0.6±0.1

A




WIRE ENTRY

2.5 REF

0.9±0.1

5.00±0.05



28.0

19.0

3.5±0.5

0.50±0.05

5.4 REF

4.1

OBSOLETE

PRELIMINARY

OBSOLETE


-	50.0	10	1-282884-7	
-	45.0	9	1-282884-6	
-	40.0	8	1-282884-5	
-	30.0	6	1-282884-4	
SEE SHEET 2	15.0	3	1-282884-3	
-	40.0	8	1-282884-2	
PRELIMINARY	SEE SHEET 2	15.0	3	1-282884-1
OBSOLETE	SEE SHEET 2	50.0	10	1-282884-0
	SEE SHEET 2	40.0	8	282884-9
	SEE SHEET 2	10.0	2	282884-8
	SEE SHEET 2	10.0	2	282884-7
	SEE SHEET 2	15.0	3	282884-6
	SEE SHEET 2	15.0	3	282884-5
	SEE SHEET 2	10.0	2	282884-4
	-	15.0	3	282884-3
	-	10.0	2	282884-2

MARKING

DIM. A

No POS.

PART NUMBER



RECOMMENDED PC BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±-
	1 PLC ±.3
	2 PLC ±.25
	3 PLC ±-
	4 PLC ±-
	ANGLES ±2

MATERIAL	FINISH

DWN	E. ZANOLINI	02NOV2001
CHK	D. BIEVENOUR	02NOV2001
APVD	D. BIEVENOUR	02NOV2001
PRODUCT SPEC	108-21066	
APPLICATION SPEC	114-20079	
WEIGHT	-	
CUSTOMER DRAWING		

STE TE Connectivity

NAME
TERMINAL BLOCK, PCB MOUNT
3RD LEVEL
STACKING W/ INTERLOCK, 5 mm PITCH

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-282884	-


SCALE 2:1 SHEET 1 OF 3 REV F3

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




282884-4 AS SHOWN




282884-5 AS SHOWN




282884-6 AS SHOWN




282884-7 AS SHOWN




282884-8 AS SHOWN




~~282884-9 AS SHOWN~~
OBSOLETE



~~282884-0 AS SHOWN~~
OBSOLETE



~~282884-1 AS SHOWN~~
OBSOLETE



~~282884-3 AS SHOWN~~
OBSOLETE



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	
mm	

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC	±-
1 PLC	±.3
2 PLC	±.25
3 PLC	±-
4 PLC	±-
ANGLES	±2
MATERIAL	FINISH

DWN	02NOV2001
E. ZANOLINI	
CHK	02NOV2001
D. BIEVENOUR	
APVD	02NOV2001
D. BIEVENOUR	
PRODUCT SPEC	108-21066
APPLICATION SPEC	114-20079
WEIGHT	-

TE Connectivity			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-282884	-

CUSTOMER DRAWING	SCALE	SHEET	OF	REV
	2:1	2	3	F3

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION 20

© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-

- 1 MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
- 2. SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3. END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.
- 4. WIRE SIZE RANGE: 16-30 AWG.
- 5. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC., FILE NO E60677.
- 6. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
- 7 NOT CUMULATIVE TOLERANCE.
- 8 INK MARKING, BLACK COLOR
- 9 PART NUMBER IS OBTAINED BY ASSEMBLYING AND GLUING TOGETHER No.4 CONNECTORS P/N 282884-2
- 10 PART NUMBER IS OBTAINED BY ASSEMBLYING AND GLUING TOGETHER No.5 CONNECTORS P/N 282884-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 02NOV2001	 TE Connectivity		
DIMENSIONS: mm		CHK D. BIEVENOUR 02NOV2001			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BIEVENOUR 02NOV2001	NAME TERMINAL BLOCK, PCB MOUNT 3RD LEVEL STACKING W/ INTERLOCK, 5 mm PITCH		
		PRODUCT SPEC 108-21066	RESTRICTED TO		
0 PLC ± 1 PLC ±.3 2 PLC ±.25 3 PLC ± 4 PLC ± ANGLES ±2		APPLICATION SPEC 114-20079	SIZE A3	CAGE CODE 00779	DRAWING NO C-282884
MATERIAL	FINISH	WEIGHT -	-		
		CUSTOMER DRAWING	SCALE 2:1	SHEET 3 OF 3	REV F3