


CW-B0037

REV	DOCUMENT	CHANGED BY	CHECK
1	JOB17991	TSM 01DEC00	
2	JOB18670	TSM 12JUL01	
3	204854	TSM 07FEB02	SAV



CHARACTERISTICS	
OPERATING FORCE-----	215 GRAMS MAX
RELEASE TRAVEL-----	.017 MIN
RELEASE FORCE-----	38 GRAM MIN
DIFFERENTIAL TRAVEL-----	.030 MAX
OVERTRAVEL-----	.053 MIN

ELECTRICAL DATA	
CONTACT ARRANGEMENT S P D T	
L156	
11A 1/3HP 125, 250 OR 277 VAC	
1/2A 125 VDC, 1/4A 250 VDC	
4A 125 VAC "L"	

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:			
	<input checked="" type="checkbox"/> US (inch) CUSTOMARY	<input type="checkbox"/> SI (mm) METRIC	
NO PLACE	X	±.040	±1
ONE PLACE	.X	±.030	±0,4
TWO PLACE	.XX	±.015	±0,15
THREE PLACE	.XXX	±.005	±
ANGLES		±	±
RAW MATERIAL-COMMERCIAL STANDARD			
THIRD ANGLE PROJECTION			

DRAWN	TSM	01DEC00
CHECK	SAV	07FEB02
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
PTC 2D	ASME Y14.5M-1994	

Honeywell			
TITLE SWITCH, BASIC			
SIZE	DWG TYPE	DRAWING NAME	REV
B	I	V7-6B19E9-022	3
SCALE	2:1	WEIGHT	SHEET 1 OF 1