


PART NO.	DIA.	"E"	"T"	"W"	"X"	"H"
8940	1/8	.315	.050	1/2	1/4	13/64
8941	3/16	.423	.050	1/2	7/32	13/64
8942	1/4	.457	.050	1/2	7/32	13/64
8943	5/16	.495	.050	1/2	7/32	13/64
8944	3/8	.529	.050	1/2	7/32	13/64
8945	7/16	.560	.050	1/2	7/32	13/64
8946	1/2	.592	.050	1/2	7/32	13/64
8947	9/16	.623	.050	1/2	7/32	13/64
8948	5/8	.654	.050	1/2	7/32	13/64
8949	11/16	.752	.050	1/2	7/32	13/64
8950	3/4	.783	.050	1/2	7/32	13/64
8951	7/8	.845	.050	1/2	7/32	13/64
8952	1	.908	.050	1/2	7/32	13/64
8955	1/8	1/8	.050	3/8	7/32	13/64
8956	3/16	.378	.050	3/8	7/32	13/64
8957	1/4	.409	.050	3/8	7/32	13/64
8958	5/16	.441	.050	3/8	7/32	13/64
8959	3/8	.471	.050	3/8	7/32	13/64
8960	7/16	.519	.050	3/8	7/32	13/64
8961	1/2	.550	.050	3/8	7/32	13/64



MATERIAL NYLON TYPE 6/6				FINISH BLACK	
DIMENSIONAL TOLERANCES				TITLE	
UNLESS OTHERWISE SPECIFIED				8940 THRU 8952	
XX	XXX	XXXX		8955 THRU 8961	
±.010	±.005			CABLE CLAMPS	
FRACTIONS	ANGLES	SCALE			
±1/64		FULL			
HEAT TREAT					
PLUT SCALE	1=1				
DRAWN B.FRANKLIN			DATE 1-3-90	SIZE	
CHECKED E.MCKINNEY			DATE 1-14-91	SD 8940-8961	
APPROVED D.MILLER			DATE 1-14-91	B	
ABBATRON Electronic Connectors and Hardware 13680 S. MOSERTOWN RD MEADVILLE, PA 16335					
ISSUE					