

D

D

C




C

B


B

A

A



P.C.B LAYOUT



PRAT NUMBER	No. of Contact	A ± 0.20	B ± 0.20	C ± 0.20	D
2301845-1	15	24.76	33.32	39.14	19.39

NOTE:

- MATERIAL:
HOUSING: PBT WITH 20% GF UL 94 V-0, BLACK COLOR
CONTACTS: PHOSPHOR BRONZE.
SHELL: STEEL
GROUNDING BRACKET: BRASS
RIVETED INSERT: BRASS
SCREWLOCK: BRASS
- FINISH:
CONTACTS: 0.36 µm [15 µ"] GOLD IN CONTACT AREA.
2.54 µm [100µ"] MATTE TIN ON SOLDER TAILS
1.27 µm [50 µ"] NICKEL UNDERPLATE OVERALL
SHELL: 2.54 µm [100µ"] NICKEL
RIVET: 1.27 µm [50 µ"] NICKEL
SCREWLOCK: 1.27 µm [50 µ"] NICKEL
BOARDLOCK: 1.27µm [50µ"] MIN NICKEL UNDERPLATE.
2.54µm [100µ"] MIN MATTE TIN PLATE
- WAVE SOLDER CAPABLE TO 265°C PER TE TEST SPEC. 109-202, CONDITION B.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	AJITH PAI	07FEB2017
CHK	DAN GORENC	07FEB2017
APVD	-	07FEB2017

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ± - 1 PLC ± 0.38 2 PLC ± 0.25 3 PLC ± 0.10 4 PLC ± - ANGLES ± 2°

MATERIAL	FINISH
-	-

PRODUCT SPEC	108-130013
APPLICATION SPEC	-
WEIGHT	0
CUSTOMER DRAWING	

15W D SKT W B/L & 4-40 INSERTS		2301845-1	
DESCRIPTION		TE PART NO	
NAME			
15 WAY D-SUB SOCKET WITH BOARD LOCK			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2301845	-
SCALE		SHEET	REV
2:1		1 of 4	G





THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



P.C.B LAYOUT

PRAT NUMBER	No. of Contact	A ± 0.20	B ± 0.20	C ± 0.20	D
2301845-2	15	24.76	33.32	39.14	19.39

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI CHK DAN GORENC	07FEB2017 07FEB2017	 TE Connectivity			
DIMENSIONS: mm		APVD —	07FEB2017	NAME 15 WAY D—SUB SOCKET WITH BOARD LOCK —			
		PRODUCT SPEC 108—130013					
		APPLICATION SPEC —					
MATERIAL —		FINISH —		SIZE A2	CAGE CODE 00779	DRAWING NO C=2301845	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 2:1	SHEET 2 of 4		REV G

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

D

D

C






C

B


B

A

A




DETAIL A



DETAIL A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI 07FEB2017	 TE Connectivity			
		CHK DAN GORENC 07FEB2017				
DIMENSIONS: mm		APVD — 07FEB2017	NAME 15 WAY D-SUB SOCKET WITH BOARD LOCK —			
	0 PLC ± —	PRODUCT SPEC 108-130013				
	1 PLC ± 0.38	APPLICATION SPEC —				
	2 PLC ± 0.25	SIZE				CAGE CODE
	3 PLC ± 0.10	—	A2	00779	C=2301845	—
4 PLC ± —	ANGLES ± —	WEIGHT 0				
MATERIAL —	FINISH —	CUSTOMER DRAWING		SCALE 3:1	SHEET 3 of 4	REV G

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



15.438	13.418	70	16	1120	2301845-2
13.422	11.402	70	16	1120	2301845-1
GROSS WEIGHT (Kg)	NET WEIGHT (Kg)	PCS/TRAY	TRAYS /CARTON	QUANTITY Pcs	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI 07FEB2017	 TE Connectivity					
		CHK DAN GORENC 07FEB2017						
DIMENSIONS: mm		APVD — 07FEB2017	NAME 15 WAY D-SUB SOCKET WITH BOARD LOCK —					
		PRODUCT SPEC 108-130013						
		APPLICATION SPEC —						
MATERIAL —		WEIGHT 0	SIZE A2	CAGE CODE 00779	DRAWING NO C=2301845		RESTRICTED TO —	
		CUSTOMER DRAWING			SCALE 1:1	SHEET 4 of 4		REV G